

Free NetCommander-AXS Management Software is available for access and control of all of your Tripp Lite NetCommander IP KVM switches (B070 and B072 series). From a single interface, you can access server ports on any of your KVM switches, power cycle or power on/off outlets of IP PDU's, and manage KVM settings. This software can be found on the model support page of the B072-032-IP4-K, or via searching NetCommander-AXS on www.tripplite.com

NetCommander 32-Port Cat5 1U Rack-Mount 4+1 User VGA USB KVM Switch with IP Remote Access with 16 USB Dongles

MODEL NUMBER: **B072-032-IP4-K**



Description

Tripp Lite's [B072-032-IP4-K](#) KVM Switch is the optimal solution for controlling up to 32 computers/servers locally, from across the room, down the street or around the globe on a network or the Internet.

This KVM switch can be accessed and controlled remotely, so there's no need to travel to the server room or network closet. A Java-based application allows access via web browser from any secure IP connection; a non-browser client that can bypass browser-related Java Security prompts is available.

The [B072-032-IP4-K](#) uses inexpensive, user-supplied Cat5e/6/6a cabling with Server Interface Units (16 included) so you can connect computers/servers located up to 100 ft. away from the switch. This switch features dual Ethernet ports and dual power supplies; if one fails, the other takes over, keeping access uninterrupted. Switch easily between the 32 ports using an on-screen display (OSD), hotkey commands or a remote toolbar. Multi-level password protection prohibits unauthorized users from accessing connected computers, and a local user and up to four remote users can each log on and access different ports simultaneously.

Two serial ports allow control of serial-manageable devices such as IP PDUs, firewalls and routers; individual ports can be assigned to an IP PDU port to power on/off the server connected to that port. This KVM switch is compatible with Windows and Linux operating systems and it supports VGA video

Highlights

- 32 ports provide control of computers/servers locally or via your network or the Internet
- Occupies just 1U of rack space
- Low-cost Cat5 cabling allows longer distances, reduces cable clutter
- Simultaneous support for 5 users – 1 local, 4 remote
- Includes 16 USB Server Interface dongles for connecting computers or servers

System Requirements

- Computer with HD15 (VGA) port, and USB port or PS/2 keyboard/mouse ports
- User-supplied Cat5e/6/6a cabling
- B078-101-USB-1 or B078-101-USB2 (USB) or B078-101-PS2 (PS/2) Server Interface Unit is required for each connected computer/server; 16 B078-101-USB-1 units are included
- Windows operating systems can remotely access the KVM via Internet Explorer, Firefox or Chrome browsers; Linux operating systems can remotely access the KVM via Firefox or Chrome browsers
- Remote console computers require minimum Pentium 4 with 2 GB memory

Package Includes



resolutions up to 1920 x 1080 @ 60 Hz. Heavy-duty steel housing stands up to frequent use.

Virtual Media allows an .iso file to be mounted to a target server and accessed as if it were stored directly on it. Virtual Media data transfer rates up to 12Mbps are supported when using a [B078-101-USB2](#) Server Interface Unit. Other features include RADIUS and LDAP/S authentication, system-sent SNMP messaging and an event log that tracks logins, reboots and network setting changes.

Free NetCommander-AXS Management Software is available to access and control all of your Tripp Lite NetCommander IP KVM switches (B070 and B072 series). From a single interface, you can access server ports on any of your KVM switches, power cycle or power on/off outlets of IP PDUs and manage KVM settings. This software can be downloaded free of charge from the model support page for the [B072-032-IP4-K](#).

Features

Saves Space and Money

- Mounts in a standard 19 in. rack
- Inexpensive Cat5e/6/6a cabling lets you locate servers up to 100 ft. from the switch
- Use a Server Interface Unit, [B078-101-USB-1](#) or [B078-101-USB2](#) (for USB) or [B078-101-PS2](#) (for PS/2) with each server that will be connected with Cat5 cable; 16 [B078-101-USB-1](#) units are included
- IP Remote Access for Fewer Trips to the Server Room
- Remote access means there's no need to travel to the server room or network closet
- Java-based application allows access via web browser; a non-browser client that can bypass browser-related Java Security prompts is available
- 1 local + 4 remote users can access different ports concurrently; up to 5 users can share a single remote session
- Supports both IPv4 and IPv6

Simplifies IT Tasks

- On-screen display, hot keys and remote toolbar for easy use
- Free NetCommander-AXS Management Software gives you remote access and control over all your Tripp Lite NetCommander IP KVM switches (B070 and B072 series)
- Video resolutions up to 1920 x 1080 @ 60 Hz are supported
- 2 serial ports allow control of serial-manageable devices such as IP PDUs, firewalls and routers; assign individual ports to an IP PDU port to power on/off the server connected to that port
- BIOS-level control of any brand and model server, regardless of the server's condition and network connectivity
- Virtual Media allows an .iso file to be mounted to a target server and accessed as if it were directly stored on it
- Virtual Media data transfer rates up to 12Mbps are supported when using a [B078-101-USB2](#) Server Interface Unit; the included [B078-101-USB-1](#) Server Interface Units can be used for Virtual Media support, but only at speeds up to 1Mbps

- [B072-032-IP4-K](#) 32-Port Cat5 4+1 User 1U Rack-Mount KVM Switch with Remote IP Access
- 16 USB Server Interface Dongles ([B078-101-USB-1](#))
- C13 to 5-15P Power Cords (x2)
- Rack-Mount Hardware
- CD with Owner's Manual
- Quick Start Guide



- Fast Virtual Media KVM System patented under Pat. No. US 9,417,720
- System-sent messages to SNMP server notify you of network failures
- Supports RADIUS and LDAP/S authentication
- Log tracks events such as logins, reboots and network setting changes on your installation

Advanced Security Features

- Multi-level password protection: create administrator accounts with full access and user accounts with limited access
- 128-bit AES and HTTPS encryption for highest security standards
- You can install SSL certificates to ensure secure transactions between web servers and browsers

Built to Last

- Flash-upgradable firmware over the network
- Heavy-duty steel housing stands up to frequent use

Specifications

MODEL TEXT	
Key Benefit	Control up to 32 computers from virtually anywhere with one Cat5 KVM switch. This KVM switch with IP remote access is a smart solution for efficient server control. Low-cost Cat5 cables let you locate servers up to 100 ft. away.
OVERVIEW	
Users	5
INPUT	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 140V AC; 200V AC; 208V AC; 220V AC; 230V AC; 240V AC
Input Frequency	50/60Hz
Input Current	120V (0.7A) / 230V (0.3A)
PHYSICAL	
Unit Dimensions (hwd / in.)	1.71 x 17.28 x 10.99
Unit Dimensions (hwd / cm)	4.34 x 43.89 x 27.91
Unit Weight (lbs.)	7.75
Unit Weight (kg)	3.52
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	0 to 80% RH, Non-Condensing



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Operating Temperature	32 to 104 F (0 to 40 C)
COMMUNICATIONS	
Port Control	Hotkeys, OSD
IP Remote Access	1
CONNECTIONS	
Ports	32
Computer/Server Ports	(x32) RJ45 Female
PC/Server Connections	USB; PS/2; VGA
SPECIAL FEATURES	
Cat5 KVM Switch	1
CERTIFICATIONS	
Approvals	UL 60950-1 (USA), CSA (Canada), FCC Part 15 Class A, CE IEC 60950-1, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>