

Protect It! Surge Protector with 6 Swivel Outlets, Direct Plug-In, 1200 Joules, Coax/Tel/Modem Protection

MODEL NUMBER: HTSWIVEL6



Description

Tripp Lite's HTSWIVEL6 Home/Business Theater Surge Suppressor provides high-performance protection--1200 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 6 outlets, 1-line coaxial protection and 1-line tel/modem protection safeguard an entire home/business theater system. \$50,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only). Includes two diagnostic LEDs, 6 ft. gold coaxial cable and 6 ft. phone cord.

Features

- 6 rotatable outlets allow for easier plug connection and removal
- 1200 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 1 set of surge-protected Type F gold coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line (2.2GHz bandwidth)
- 1 set of surge-protected tel/modem connectors (with included 6 ft. phone cord) safeguard personal video recorders (PVRs) on a single dial-up line
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into six by plugging into any wall outlet
- \$50,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Highlights

- 6 rotatable outlets
- Direct plug-in design
- 1200 joule rating
- 1 line tel/modem and 1-line gold coax (2.2GHz bandwidth) protection
- \$50,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

Package Includes

- HTSWIVEL6 Surge Suppressor
- Instruction manual with warranty information
- 6 ft. gold coaxial cable
- 6 ft. phone cord



Specifications

OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Outlet Orientation	Rotatable
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	0
Input Cord Length (m)	Direct plug-in
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Right-Angle Plug	0
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1200
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400, 500, 500
EMI / RFI Filtering	Up to 20 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	1
Telephone/DSL Protection Details	1 line



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable (Coax) Protection	1
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	0
PHYSICAL	
Shipping Dimensions (hwd / in.)	8.6 x 5.8 x 2.38
Shipping Dimensions (hwd / cm)	21.84 x 14.73 x 6.05
Shipping Weight (lbs.)	1.0
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	6.25 x 4 x 2.25
Unit Dimensions (hwd / cm)	15.88 x 10.16 x 5.72
Unit Weight (lbs.)	0.6
Unit Weight (kg)	0.27
Material of Construction	Plastic
Receptacle Color	Black
Outlets Measurement (Center to Center)	29mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
cUL / CSA (Canada)	cUL
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>