
X8R/X8L Dielectric








AVX has developed a range of multilayer ceramic capacitors designed for use in applications up to 150°C. These capacitors are manufactured with an X8R and an X8L dielectric material. X8R material has capacitance variation of ±15% between -55°C and +150°C. The X8L material has capacitance variation of ±15% between -55°C to 125°C and +15/-40% from +125°C to +150°C.

The need for X8R and X8L performance has been driven by customer requirements for parts that operate at elevated temperatures. They provide a highly reliable capacitor with low loss and stable capacitance over temperature.

They are ideal for automotive under the hood sensors, and various industrial applications. Typical industrial application would be drilling monitoring system. They can also be used as bulk capacitors for high temperature camera modules.

Both X8R and X8L dielectric capacitors are automotive AEC-Q200 qualified. Optional termination systems, tin, FLEXITERM® and conductive epoxy for hybrid applications are available. Providing this series with our FLEXITERM® termination system provides further advantage to customers by way of enhanced resistance to both, temperature cycling and mechanical damage.

PART NUMBER (see page 2 for complete part number explanation)



NOTE: Contact factory for availability of Termination and Tolerance Options for Specific Part Numbers.



			X	3R											X8L							
SIZE		0	0603		0805		1206		SIZE		0603		0805			1206						
	WVDC	25V	50V	25V	50V	25	5V 50V	_		WVI	DC	25V	50V	100V	25V	50V	100V	16V	25V	50V	100V	
331	Cap 330	G	G	J	J				331	Cap	330		G	G		J	J					
471	(pF) 470	G	G	J	J				471	(pF)	470		G	G		J	J				1	
681	680	G	G	J	J				681		680		G	G		J	J					
102	1000	G	G	J	J	J	J		102		1000		G	G		J	J					
152	1500	G	G	J	J	J	J		152		1500		G	G		J	J			J	J	
222	2200	G	G	J	J	J	J		222		2200		G	G		J	J			J	J	
332	3300	G	G	J	J	J	J		332		3300		G	G		J	J			J	J	
472	4700	G	G	J	J	J	J		472		4700		G	G		J	J			J	J	
682	6800	G	G	J	J	J			682		6800		G	G		J	J			J	J	
103	Cap 0.01	G	G	J	J	J			103		0.01		G	G		J	J			J	J	
153	(μF) 0.015	G	G	J	J	J	J		153		0.015	G	G		J	J	J			J	J	
223	0.022	G	G	J	J	J	J		223		0.022	G	G		J	J	J			J	J	
333	0.033	G	G	J	J	J	J		333		0.033	G	G		J	J	N			J	J	
473	0.047	G	G	J	J	J			473		0.047	G	G		J	J	N			J	J	
683	0.068	G		N	N	N			683		0.068	G	G		J	J				J	J	
104	0.1			N	N	N			104		0.1	G	G		J	J				J	M	
154	0.15			N	N	N			154		0.15				J	N		J	J	J	Q	
224	0.22			N		N			224		0.22				N	N		J	J	J	Q	
334	0.33					N			334		0.33				N			J	М	Р	Q	
474	0.47					N	1		474		0.47				N			M	М	Р		
684	0.68								684		0.68							M				
105	1								105		1							M				
	WVDC	25V	50V	25V	50V	25				WVI	DC	25V	50V	100V	25V	50V	100V	16V	25V	50V	100V	
SIZE		0603			0805		1206			SIZE			0603		0805		1206					
Lette	r A	С	CE		G	J	K	Λ	Л	N		Q		Х	Υ		Z		= AEC-Q200			
Max.	0.33	0.5	6 0.7	1 (0.90	0.94	94 1.02		27	1.40	1.40 1.		52 1.78		.29	2.54 2		1.79			Qualified	
Thickne						0.037)	(0.040)	(0.0)		(0.055)		060)	(0.070)		090)	(0.100		.110)				
	PAPER EMBOSSED																					




X8R/X8L Dielectric

General Specifications

APPLICATIONS FOR X8R AND X8L CAPACITORS

- All market sectors with a 150°C requirement
- Automotive on engine applications
- Oil exploration applications
- Hybrid automotive applications
 - Battery control
 - Inverter / converter circuits
 - Motor control applications
 - Water pump
- Hybrid commercial applications
 - Emergency circuits
 - Sensors
 - Temperature regulation






ADVANTAGES OF X8R AND X8L MLC CAPACITORS

- Both ranges are qualified to the highest automotive AEC-Q200 standards
- Excellent reliability compared to other capacitor technologies
- RoHS compliant
- Low ESR / ESL compared to other technologies
- Tin solder finish
- FLEXITERM® available
- Epoxy termination for hybrid available
- 100V range available

ENGINEERING TOOLS FOR HIGH VOLTAGE MLC CAPACITORS

- Samples
- Technical Articles
- Application Engineering
- Application Support





X8R/X8L Dielectric



Specifications and Test Methods

Parame		X8R/X8L Specification Limits	Measuring Conditions					
Operating Temp		-55°C to +150°C	Temperature Cycle Chamber					
Capac	itance	Within specified tolerance	Freq.: 1.0 kHz ± 10%					
Dissipation	on Factor	\leq 2.5% for \geq 50V DC rating \leq 3.5% for 25V DC and 16V DC rating	Voltage: 1.0Vrms ± .2V					
Insulation I	Resistance	100,000ΜΩ or 1000ΜΩ - μ F, whichever is less	Charge device with rated voltage for 120 ± 5 secs @ room temp/humidity					
Dielectric	Strength	No breakdown or visual defects	Charge device with 300% of rated voltage for 1-5 seconds, w/charge and discharge current limited to 50 mA (max) Note: Charge device with 150% of rated voltage for 500V devices.					
	Appearance	No defects	Deflection: 2mm Test Time: 30 seconds					
Resistance to	Capacitance Variation	≤ ±12%						
Flexure Stresses	Dissipation Factor	Meets Initial Values (As Above)	1mm/sec					
	Insulation Resistance	≥ Initial Value x 0.3	90 mm —					
Solder	rability	≥ 95% of each terminal should be covered with fresh solder	Dip device in eutectic solder at 230 ± 5°C for 5.0 ± 0.5 seconds					
	Appearance	No defects, <25% leaching of either end terminal						
	Capacitance	≤ ±7.5%						
	Variation		Dip device in eutectic solder at 260°C for 60 seconds. Store at room temperature for 24 ± 2 hours before measuring electrical properties.					
Resistance to Solder Heat	Dissipation Factor	Meets Initial Values (As Above)						
Joinel Heat	Insulation Resistance	Meets Initial Values (As Above)						
	Dielectric Strength	Meets Initial Values (As Above)						
	Appearance	No visual defects	Step 1: -55°C ± 2°	30 ± 3 minutes				
	Capacitance Variation	≤ ±7.5%	Step 2: Room Temp	≤ 3 minutes				
Thermal Shock	Dissipation Factor	Meets Initial Values (As Above)	Step 3: +125°C ± 2°	30 ± 3 minutes				
SHOCK	Insulation Resistance	Meets Initial Values (As Above)	Step 4: Room Temp	≤ 3 minutes				
	Dielectric Strength	Meets Initial Values (As Above)		eat for 5 cycles and measure after 2 hours at room temperature				
	Appearance	No visual defects						
	Capacitance Variation	≤ ±12.5%	Charge device with 1.5 rated voltage (≤ 10V) in test chamber set at 150°C ± 2°C					
Load Life	Dissipation Factor	≤ Initial Value x 2.0 (See Above)	for 1000 hou	ırs (+48, -0)				
	Insulation Resistance	≥ Initial Value x 0.3 (See Above)	Remove from test chamber and stabilize at room temperature for 24 ± 2 hours before measuring.					
	Dielectric Strength	Meets Initial Values (As Above)						
	Appearance	No visual defects	Ctoro in a toot about	or oot at 9500 : 000/				
	Capacitance Variation	≤ ±12.5%	Store in a test chamber set at 85°C ± 2°C/85% ± 5% relative humidity for 1000 hours (+48, -0) with rated voltage applied.					
Load Humidity	Dissipation Factor	≤ Initial Value x 2.0 (See Above)						
	Insulation Resistance	≥ Initial Value x 0.3 (See Above)	Remove from chamber and stabilize at room temperature and humidity for 24 ± 2 hours before measuring.					
	Dielectric Strength	Meets Initial Values (As Above)						

