


## 1.9kW Single-Phase 120V Basic PDU, 14 NEMA 5-15/20R Outlets, NEMA L5-20P Input w/5-20P Adapter, 15 ft. Cord, 0U Vertical

MODEL NUMBER: PDUV20



### Highlights

- NEMA L5-20P input with 15 ft. cord and 5-20P adapter
- 14 NEMA 5-15/20R outlets
- Switchless design prevents accidental shutdown
- 36 in. all-metal housing
- Supports toolless 0U vertical mounting

### Package Includes

- PDUV20 1.9kW Single-Phase 120V Basic PDU
- NEMA 5-20P plug adapter
- Mounting hardware
- Owner's manual

### Description

The PDUV20 1.9kW Single-Phase 120V Basic PDU is an excellent no-frills unit for data centers, server rooms and network wiring closets. Perfectly suited for high-density IT environments, the PDUV20 features 14 NEMA 5-15/20R outlets. The NEMA L5-20P input plug with long 15-foot (4.5 m) cord connects to your facility's compatible AC power source, generator or protected UPS to distribute power to connected equipment. An included adapter converts the input plug to NEMA 5-20P.

The switchless design prevents an accidental shutdown, which could lead to costly downtime. A 20A circuit breaker protects connected equipment from dangerous overloads. The 36-inch all-metal housing supports 0U vertical mounting in EIA-standard 19-inch racks using the included hardware and mounting clips or toolless mounting using the included buttons. You can also mount the PDUV20 on a wall or workbench or under a counter with user-supplied hardware.

### Features

#### Reliable Single-Phase Power Distribution

- Versatile no-frills PDU for data centers, server rooms and network wiring closets
- 14 NEMA 5-15/20R outlets
- NEMA L5-20P input with 15 ft. cord and 5-20P adapter
- 20A circuit breaker protects outlets against overloads

#### Switchless Design

- Prevents accidental shutdowns and costly downtime

#### Versatile Installation Options



- 36 in. all-metal housing
- Supports toolless 0U vertical mounting in EIA-standard 19 in. racks
- Also supports 0U mounting using included hardware
- Rear installation buttons can be relocated to the left or right surface for rear, center or forward-facing outlet orientation
- Also mounts on wall, workbench or under a counter with user-supplied hardware

## Specifications

MODEL TEXT	
Key Benefit	Delivers 120V single-phase AC power to multiple loads from a utility outlet, generator or UPS system in a high-density IT environment. Recommended for data centers, server rooms and network wiring closets.
OVERVIEW	
PDU Type	Basic
OUTPUT	
Output Capacity Details	2.03kW (127V), 1.92kW (120V), 1.6kW (100V) / 20A total capacity (Agency de-rated to 16A); 16A max per outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15/20R
Output Nominal Voltage	100; 120; 127
Overload Protection	20A circuit breaker
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	20A 120V
Maximum Input Amps	16
PDU Plug Type	NEMA 5-20P; NEMA L5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Phase	Single-Phase
USER INTERFACE, ALERTS & CONTROLS	
Switches	n/a
PHYSICAL	
Shipping Dimensions (hwd / in.)	40 x 3 x 2.75



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Dimensions (hwd / cm)	101.6 x 7.62 x 6.99
Shipping Weight (lbs.)	5.3
Shipping Weight (kg)	2.40
Unit Dimensions (hwd / in.)	36 x 1.75 x 1.25
Unit Dimensions (hwd / cm)	91.44 x 4.45 x 3.18
Unit Weight (lbs.)	4
Unit Weight (kg)	1.81
Material of Construction	Metal
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
PDU Form Factor	0U; Vertical
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>