

SmartPro 230V 1.5kVA 940W Line-Interactive UPS, Tower, DB9, 6 Outlets

MODEL NUMBER: **SMARTINT1500**



Description

The SMARTINT1500 SmartPro 230V 1.5kVA 940W Line-Interactive UPS provides battery backup and AC power protection against blackouts, brownouts, power surges and line noise that can damage electronics or destroy data. Ideal for backing up VoIP systems, point-of-sale applications and network closets, the SMARTINT1500 switches to battery mode in milliseconds to keep your connected equipment running long enough to save files and shut down safely with no data loss.

Featuring six IEC-320-C13 outlets and two C13-to-C14 power cords, the SMARTINT1500 has an internal battery that provides 20 minutes of support at half load and seven minutes at full load. Front-panel LEDs indicate line power, battery power, load level, voltage regulation and battery status. An alarm sounds to indicate power failure or a low battery.

Automatic voltage regulation (AVR) maintains 230V nominal output over an input range of 165V to 277V without using battery power. EMI/RFI noise filtering improves your equipment's performance and prevents damage. A 480-joule surge suppression rating protects your equipment from harmful power surges. With Tripp Lite's PowerAlert software (available via free download), SMARTINT1500 enables safe unattended system shutdown and file saves in case of a prolonged power failure.

Features

Protects Mission-Critical Equipment

- Provides fully regulated AC output for VoIP systems, point-of-sale applications and network closets
- Audible alarm signals loss of utility power or low battery
- 6 IEC-320-C13 outlets
- C14 inlet
- 480-joule surge suppression rating

Highlights

- Corrects under- and overvoltages from 165V to 277V
- 6 IEC-320-C13 outlets
- Front-panel LEDs indicate load, power and battery statuses
- Monitoring of power conditions via PowerAlert®
- 20 min. runtime at half load; 7 min. at full load

Package Includes

- SMARTINT1500 SmartPro 230V 1.5kVA 940W Line-Interactive UPS
- (2) IEC-320 C13-to-C14 power cables
- (2) DB9 cables
- Owner's manual



Reliable Battery Backup

- Supports half load up to 20 min. and full load up to 7 min.
- Internal batteries designed for hot-swap field replacement
- 94% line-power efficiency rating saves money in energy costs
- Cold-start capability enables turn-on in battery mode during blackouts

Automatic Voltage Regulation (AVR)

- Maintains 230V nominal output over input range of 165V–277V without using battery power

EMI/RFI Line Noise Filtering

- Removes electromagnetic and radio frequency interference that can disrupt or damage equipment's performance

LED Indicators

- Front-panel LEDs signal indicate line power, battery power, load level, voltage regulation and battery status

Communications Port

- DB9 port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert

Small-Footprint Tower Housing

- Mounts on wall with optional UPSWM accessory

Specifications

MODEL TEXT	
Key Benefit	Protects connected mission-critical equipment against damage, downtime and data loss due to blackouts, brownouts, power surges and line noise. Ideal solution for VoIP systems, point-of-sale applications and network closets.
OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output kVA Capacity (kVA)	1.5
Output Watt Capacity (Watts)	940
Nominal Output Voltage(s) Supported	220V; 230V; 240V
Nominal Voltage Details	230V nominal output in battery mode



Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	-15%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(6) C13
Included Output Power Cables	Includes 2 C13 to C14 output power cables
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	6.5A
Nominal Input Voltage(s) Supported	230V AC
UPS Input Connection Type	C14 inlet
Input Circuit Breakers	10A
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	7 min. (940w)
Half Load Runtime (min.)	20 min. (470w)
DC System Voltage (VDC)	36
Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90% (typical, full load discharge)
Internal UPS Replacement Battery Cartridge	<u>RBC53</u>
Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries
Expandable Runtime	No
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 166 to 277
Overvoltage Correction	Input voltages between 243 and 277 are reduced by 12%
Undervoltage Correction	Input voltages between 191 and 215 are boosted by 10%
Severe Undervoltage Correction	Input voltages between 165 and 190 are boosted by 22%
USER INTERFACE, ALERTS & CONTROLS	



Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Optional Accessories	Wallmount (UPSWM - tower mounting kit)
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	12.8 x 7.5 x 9.2
UPS Power Module Dimensions (hwd, cm)	32.51 x 19.05 x 23.37
UPS Power Module Weight (lbs.)	38.6
UPS Power Module Weight (kg)	17.51
UPS Shipping Dimensions (hwd / in.)	18.2 x 12 x 13.8
UPS Shipping Dimensions (hwd / cm)	46.23 x 30.48 x 35.05
Shipping Weight (lbs.)	43.2
Shipping Weight (kg)	19.6
UPS Housing Material	Polycarbonate
Primary UPS Height (mm)	325
Primary UPS Width (mm)	190
Primary UPS Depth (mm)	234
Shipping Height (mm)	462
Shipping Width (mm)	305
Shipping Depth (mm)	351
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Relative Humidity	0 to 95%, non-condensing
AC Mode Efficiency Rating (100% Load)	94%
COMMUNICATIONS	
Communications Interface	DB9 Serial; Contact closure
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; contact closure communications via 2nd DB9 port (2 total)
PowerAlert Software	For local monitoring via the UPS's built-in DB9 port, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	2 DB9 cables included
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	165
High Voltage Transfer to Battery Power (Setpoint)	n/a
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); CE; Tested to GOST (Russia); Tested to SASO (Saudi Arabia); Tested to IRAM (Argentina)
UPS Certification Details	EMI approvals 62040
WARRANTY	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>