

559/560 Series Fuse Holders for TE5/TR5 Type Fuses




559 Series Holder


560 Series Holder

Dimensions units in mm

559 Series



560 Series



Product Characteristics		
	559 Series (Lead Free)	560 Series
Compatible Fuses	TR5/TE5	TR5/TE5
Materials	Holder: Black Thermoplastic, UL94 V-0 Polyamide PA 6.6	Holder: Thermoplastic, UL 94 V-0 Polyester PET
	Metal Parts: Copper alloy; solderable tinned	
Electrical Data (23°C)	Rated Voltage: 250V	
	Max. Current/Power: 6.3 A / 1.6 W	
Mounting	PC Board, 7.18 mm pin spacing	PC Board, 5.08 mm pin spacing
Solderability	max. 260 °C, 10 s (Wave)	
Minimum Cross Section	Conducting path - 0.1 mm ²	
Unit Weight	0.63 g	0,4 g

Note: Ensure proper fuseholder de-rating.

Ordering Information		
Ordering Number	"A" Height Options	Packaging
559 0000 00 01	6.5 mm (code 0001)	1000 Pcs Bulk
559 0000 80 11	10 mm (code 8011)	100 Pcs Bulk
560 0000 13 19 ¹	3.0 mm (code 1319)	500 Pcs Bulk
560 0000 10 09 ¹	4.3 mm (code 1009)	1000 Pcs Bulk
560 0000 10 19 ¹	4.3 mm (code 1019)	500 Pcs Bulk

1. UL Recognized.

Additional Information



Datasheet 559 Series



Resources 559 Series



Samples 559 Series



Datasheet 560 Series



Resources 560 Series



Samples 560 Series