

## Protect It! 7-Outlet Surge Protector, 7 -ft. Cord, 2160 Joules, Coaxial Protection

MODEL NUMBER: **SUPER7COAX**



### Description

The SUPER7COAX surge suppressor from Tripp Lite has 7 outlets and a 7-ft. cord with a space-saving right-angle plug. The unit has 2160 joules of surge energy absorption to handle the strongest surges. Built-in 2.2 GHz gold coax jacks prevent surges from damaging your cable/satellite equipment. Diagnostic LEDs alert the user to potential power problems. \$75,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only).

### Features

- 7 outlets
- 7-ft. cord with space-saving right-angle plug
- Surge suppression rating: 2160 joules
- 1 set of 2.2 GHz gold coaxial jacks
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$75,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only) covers connected equipment
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

## Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz

### Highlights

- 7 outlets/7 ft. cord
- 2160 joule rating
- 2.2 GHz gold coaxial surge protection
- \$75,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

### Package Includes

- Super7Coax Surge Suppressor
- 6-ft gold coax cable
- Warranty information with instruction manual



Output Receptacles	(7) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total
Outlet Orientation	Single row of 5, plus 2 side mounted outlets
Right-Angle Outlets	0
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	7
Input Cord Length (m)	2.13
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Right-Angle Plug	1
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Two position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	2160
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330V L-G; 400V L-N; 400V N-G
EMI / RFI Filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	0
Cable (Coax) Protection	1
Cable (Coax) Protection Details	1 line



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Network (Ethernet) Protection	0
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	12.40 x 5.90 x 1.77
Shipping Dimensions (hwd / cm)	31.50 x 14.99 x 4.50
Shipping Weight (lbs.)	1.56
Shipping Weight (kg)	0.71
Unit Dimensions (hwd / in.)	1.54 x 2.72 x 10.3
Unit Dimensions (hwd / cm)	3.91 x 6.91 x 26.16
Unit Weight (lbs.)	1.39
Unit Weight (kg)	0.63
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light gray
Color (AC Line Cord)	Light Gray
Outlets Measurement (Center to Center)	Between Standard Outlets = 29mm; Between Transformer Outlets = 48mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance Between Slots = 78mm; Distance Between Slot Height = 24mm
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>