

Protect It! 7-Outlet Surge Protector, 7-ft. Cord, 1080 Joules, Tel/Modem Protection, Silver Housing

MODEL NUMBER: TLP707TEL



Highlights

- 7 outlets / 7-ft. cord
- 1080 joule rating
- 1 in/1 out tel/modem surge protection
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- TLP707TEL surge suppressor
- 6-ft. RJ11 cable
- Instruction manual and warranty information

Description

Tripp Lite's TLP707TEL surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TLP707TEL offers 7 total outlets, 7 foot cord with space-saving angled plug, automatic cord management and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive metallic silver housing with 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/7-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Unique on-end suppressor format supports the connection of up to 3 large transformer plugs on one side and 4 additional straight input plugs on the other

SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL1449 3rd Edition

Features

- Offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics
- Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges
- Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more



- 7 total outlets
- 7 foot cord with space-saving angled plug, automatic cord management
- Diagnostic LEDs to warn of wiring problems and suppressor damage
- Heavy grade AC suppression rated at 1080 joules shields equipment from surges and line noise
- Attractive metallic silver housing
- 3 designated transformer plug outlets offer convenient protection of desktop computer equipment and accessories
- \$50,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(7) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Overload Protection	15A resettable combo switch / circuit breaker
Transformer Accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total
Outlet Safety Covers	Includes built-in sliding outlet safety covers
Outlet Orientation	Two rows of outlets, 3 widely spaced on one side for transformers, 4 closely spaced outlets on the other
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	7
Input Cord Length (m)	2.13
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Right-Angle Plug	1



USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Up to 20dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	1
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
PHYSICAL	
Shipping Dimensions (hwd / in.)	12.40 x 4.92 x 2.25
Shipping Dimensions (hwd / cm)	31.50 x 12.50 x 5.72
Shipping Weight (lbs.)	1.41
Shipping Weight (kg)	0.64
Unit Dimensions (hwd / in.)	1.97 x 1.61 x 10.91
Unit Dimensions (hwd / cm)	5.00 x 4.09 x 27.71
Unit Weight (lbs.)	1.25
Unit Weight (kg)	0.57
Material of Construction	Plastic
Housing Color	Metallic Silver
Receptacle Color	Gray
Color (AC Line Cord)	Black
Form Factors Supported	Supports floor / desktop placement
Outlets Measurement (Center to Center)	Transformer Side Spacing = 61.8mm; Standard Outlet Side Spacing = 25.4mm



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>