

175 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 2/0 #14 AWG
- Load: (1) 2/0 #14 AWG

Electrical Ratings

- 175 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- Short circuit current ratings (SCCR): See SCCR section below for specifications
- CU7AL 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring

Agency Compliance

- UR UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA certifed to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1

Material Information

- Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Connector: aluminum, tin plated
- Terminal screws: aluminum, tin plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant

marathon™ _____Special Products

Product Data Sheet

132X572 Replace "x" with 1, 2, or 3 for number of poles

Power Terminal Block

A Regal Brand



www.marathonsp.com

www.regalbeloit.com

marathon[™]

Termination Specifications

Line & Load Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹	
	2/0 - 1/0	13.6 N·m (120 lbf·in)	1	В, С	
	1 - 6	13.6 N·m (120 lbf·in)	1	B, C, G, H, I (DLO)	
	8 4.5 N·m (40 lbf·in)		1	B, C, G, H, I (DLO)	
	10 - 14	4 N·m (35 lbf·in)	1	B, C, I (DLO)	

- Aluminum stranded wire range: 2/0 #6 AWG
- Solid copper wire range: 10 14 AWG
- Wire strip length: 3/4 in. (19mm)
- Terminal screw drive: 5/16 in. hex

¹ For information on copper stranded wire classes please reference: http://www.marathonsp.com/CatalogPDFs/Flexible-Stranded-Wire.pdf

Short Circuit Current Ratings (SCCR)

- The suitable conductor ranges are limited to the table values only for achieving the SCCR in excess of the default rating of 10,000A.
- Other conductor combinations within the "Terminal Specifications" noted are suitable for achieving a SCCR of 10,000A (the default rating of terminal blocks).
- Enclosure size Investigated with a minimum 16x12x6 enclosure. Use in smaller enclosures is subject to end use evaluation.

Wire Type	Suitable Conductors		Max Overcurrent Protection Fuse Required Amp Rating / Class					SCCR RMS Sym. Amps	
	Line	Load	J	Т	RK1	RK5	G	СС	600V. Max
B, C	2/0 - 6	2/0 - 6	200	200	200	100	60	30	100,000
G, H, I	1 - 6	1 - 6	150	150	100	30	60	30	100,000
(*)	2/0 - 14	2/0 - 14	None					10,000	

SCCR With Fuses

* Any wire class evaluated (see terminal specification section)

marathon[™] _____Special Products

Installation & Accessories

- Mounting (Panel or Din):
 - For use with #10 fastener.
 - Torque mounting fastener to 25-30 lbf·in (2.8 3.4 N·m).
 - 7.5 X 35 mm din rail mountable
- Covers:
 - Snap on, hinge covers available upon request
 - Catalog Number: CC132x (replace "x" with number of poles)
 - Covers are black thermoplastic
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Insulator base adders and 1 pole product can be snapped together through integral dovetails to create variable pole power blocks
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications
- End bracket for din rail mounting: MSK35

Drawing

