



**PROTECTIVE INDUSTRIAL PRODUCTS**

# 150-0-14 Specification Sheet

## NOVAX RUBBER INSULATING GLOVES

### PRODUCT DESCRIPTION:

Novax rubber electrical insulating gloves, black, class 0, 14-inch, smooth finish.

- Meet ANSI/ASTM D120 standard and NFPA 70E for use around electrical hazards and arc flash protection.
- Contoured shape reduces hand fatigue.
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability.
- Silicone free.

### Applications:

Used exclusively for electrical purposes, such as power generation, electrical contractors, hybrid automotive repair/service, hybrid automobile manufacturing, industrial plant maintenance, utilities.

### TECHNICAL DATA:

Shell: Natural rubber

Color: Black

Cuff Style: Rolled

Available Sizes: 7-11

Packaging: 1 pair per bag/box, 12 pair per case

Case Dimensions: cm - 43 x 43 x 32.5 / in - 16.9 x 16.9 x 12.8

Case Weight: 17.6 lbs / 8.0 kg

Manufacturer Certifications: ISO9001:2000 certified

Country of Origin/Harmonization Code: Malaysia/4015.19.1050

### MAX USE VOLTAGE:

	AC V rms	DC V
Class 0	1,000	1,500

**10**

NOVAX™ by G.B. INDUSTRIES  
ANSI / ASTM CLASS 0  
MADE IN MALAYSIA  
D120 TYPE I  
MAX USE VOLT 1000V AC

### BARCODE #

### PAIR


### CASE

150-0-14/7	01616314066558	02616314066557
150-0-14/8	01616314066541	02616314066540
150-0-14/9	01616314066534	02616314066533
150-0-14/10	01616314066565	02616314066564
150-0-14/11	01616314066572	02616314066571



### DIMENSIONS:

Size Available	7	8	9	10	11	12
Over Length (cm) – A (in)	36.0 14.0	36.0 14.0	36.0 14.0	36.0 14.0	36.0 14.0	36.0 14.0
Palm Width (cm) – B (in)	9.0 3.5	10.0 3.9	10.5 4.1	12.0 4.7	13.5 5.3	15.0 5.9
Max thickness (mm)	1.02	1.02	1.02	1.02	1.02	1.02



This document is the property of PIP and the information contained herein is proprietary to PIP.