

# COAXIAL ATTENUATORS

## TNC

### 1 - 2 WATTS

Part Number	Frequency range (GHz)	ATTENUATION (dB)			V.S.W.R.		Power (W)		Fig.
		Nom.	DEVIATION		DC - 2	2 - 3	avg.	peak	
			DC - 2	2 - 3					
R412500000	DC - 2	0	+ 0.35		≤ 1.15		2	100	1
R412501000		1	± 0.35		≤ 1.15		2	100	1
R412502000		2	± 0.35		≤ 1.15		2	100	1
R412503000		3	± 0.35		≤ 1.15		2	100	1
R412504000		4	± 0.35		≤ 1.15		2	100	1
R412505000		5	± 0.35		≤ 1.15		2	100	1
R412506000		6	± 0.35		≤ 1.15		2	100	1
R412507000		7	± 0.35		≤ 1.15		2	100	1
R412508000		8	± 0.35		≤ 1.15		2	100	1
R412509000		9	± 0.35		≤ 1.15		2	100	1
R412510000		10	± 0.35		≤ 1.15		2	100	1
R412511000		11	± 0.35		≤ 1.15		2	100	1
R412512000		12	± 0.35		≤ 1.15		2	100	1
R412513000		13	± 0.35		≤ 1.15		2	100	1
R412514000		14	± 0.35		≤ 1.15		2	100	1
R412515000		15	± 0.35		≤ 1.15		2	100	1
R412520000		20	± 0.45		≤ 1.15		2	100	1
R412530000		30	± 0.80		≤ 1.15		2	100	2
R412540000		40	± 0.80		≤ 1.15		2	100	2
R412550000		50	± 1.00		≤ 1.15		2	100	2
R412500124	DC - 3	0	+ 0.3	+ 0.5	≤ 1.20	≤ 1.30	1	100	3
R412501124		1	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412502124		2	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412503124		3	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412504124		4	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412505124		5	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412506124		6	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412507124		7	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412508124		8	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412509124		9	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412510124		10	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412511124		11	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412512124		12	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412513124		13	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412514124		14	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412515124		15	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412516124		16	± 0.7	± 0.7	≤ 1.20	≤ 1.30	1	100	3
R412517124		17	± 0.7	± 0.7	≤ 1.20	≤ 1.30	1	100	3
R412518124		18	± 1.0	± 1.0	≤ 1.20	≤ 1.30	1	100	3
R412519124		19	± 1.0	± 1.0	≤ 1.20	≤ 1.30	1	100	3
R412520124		20	± 1.0	± 1.0	≤ 1.20	≤ 1.30	1	100	3





Figure	A inch (mm)	B inch (mm)	Weight (g)
1	1.79" (45.5)	.51" (13)	30
2	2.21" (56.1)		40
3	1.26" (32)		17