

RIMLESS

MEETS ANSI
Z87.1+



DESCRIPTION

Trendy design that hits the mark with a lens treatment to fit your application

- Lightweight, rimless design offers optimal protection
- Flexible bayonet style temples provide a secure fit
- Molded nose bridge design to fit the vast majority of users
- FogLess™ lens coating as standard (except on clear AR lens)
- Also meets CSA Z94.3 requirements for Canada
- 9 Base curve lens



Polycarbonate lenses block 99.99% of the sun's ultraviolet rays. This ultraviolet protection has already been incorporated within the lens material when the lenses are being produced.

TECHNICAL DATA

LENS	
TYPE	Dual
MATERIAL	Polycarbonate 99.99% UVA and UVB light absorption
THICKNESS	2.2 mm
BASE CURVE	9
TEMPLES	
DESIGN	Rimless
MATERIAL	Polycarbonate
SAFETY STANDARDS	
ANSI Z87.1	Yes
CAN/CSA Z94.3	Yes
PACKAGING	
PACKAGING	12 per inner display box; 144 pair per case
CASE SIZE	cm: 59.3 x 36 x 40.5 in: 23.3 x 14.2 x 15.9
CASE WEIGHT	6.9 kg / 15.2 lbs
SINGLE PAIR WEIGHT	26 gr / 0.92 oz
COUNTRY OF ORIGIN	Taiwan
HARMONIZATION CODE	9004.90.0000

IDEAL FOR INDUSTRIAL WORKERS, INSPECTION & OUTSIDE WORK

ITEM NUMBERS & BARCODES

ITEM #	TEMPLE COLOR	LENS COLOR & COATING	UPC BARCODES		
			EACH	BOX	CASE
250-31-0020	Clear	Clear, Anti-Scratch/Anti-Fog	616314130199	01616314130198	02616314130197
250-31-0021	Gray	Gray, Anti-Scratch/Anti-Fog	616314130205	01616314130204	02616314130203
250-31-0023	Light Blue	Light Blue, Anti-Scratch/Anti-Fog	616314130212	01616314130211	02616314130210
250-31-0029	Amber	Amber, Anti-Scratch/Anti-Fog	616314130229	01616314130228	02616314130227
250-31-0010	Clear	Clear, Anti-Reflective/Anti-Scratch	616314130236	01616314130235	02616314130234
250-31-0026	Translucent Gray	Blue Mirror, Anti-Scratch/Anti-Fog	616314130243	01616314130242	02616314130241
250-31-0226	Translucent Brown	Indoor/Outdoor Blue, Anti-Scratch/Anti-Fog	616314130250	01616314130259	02616314130258
250-31-0031	Clear	Gradient, Anti-Scratch/Anti-Fog	616314130267	01616314130266	02616314130265