

Rittal – The System.

Faster – better – everywhere.

► **Tangential fans for
482.6 mm (19") Air
throughput 320 m³/h –
SK 3144.000**

Date : Mar 19, 2018

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Tangential fans for 482.6 mm (19") Air throughput 320 m³/h – SK 3144.000

created: 19.03.2018 build on www.rittal.com/us-en



Product description

Supply includes: Wired unit ready for connection
Filter mat

Product features

Total cooling output/number of fan modules required:

Air throughput (unimpeded air flow): 320 m³/h (188.3 cfm)

Rated operating voltage: 230 V, 1~, 50 Hz/60 Hz

Dimensions: Height: 88 mm (3.5 ")
Width: 482.6 mm (19 ")
Depth: 158 mm (6.2 ")

Temperature range: Operation (environment): -10°C...+55°C

Rated power P_{el}: At 50 Hz: 37 W

Rated current (max.): At 50 Hz: 0.16 A

Noise pressure level: At 50 Hz: 52 dB(A)

Maximum static pressure difference: 65 Pa - 70 Pa

Speed:	2245 rpm
Packaging unit:	1 pc(s).
Weight/packaging unit:	2.02 kg (4.5 lb.)
EAN:	4028177037137
Customs tariff number:	84145915
ETIM 6.0:	EC000320
ETIM 5.0:	EC000320
eCl@ss 8.0/8.1:	27180716
eCl@ss 7.0/7.1:	27180716
eCl@ss 6.0/6.1:	27180716
eCl@ss 5.1/5.1.4:	27180705
Product description (long):	SK tangential fan, for 482.6 mm (19"), 320 m ³ /h, 230 V, 50/60 Hz, WHD: 482.6 x 88 x 158 mm
Approvals	
Approvals:	Approval overview
Certificates:	EAC
Declarations:	Declaration of conformity