WWW.PHIHONG.COM

20-30 Watt Universal 3-Wire Input Adapter **PSC30U** Adapter Series Meets CEC and EISA Requirements













Features

- Low Cost
- **EISA Energy Efficiency Compliance**
- Class B EMI

- Non-Vented/Spill-proof Case
- Low Profile Design

Applications

- Portable Equipment
- Peripherals

- Networking
- **Gaming Machines**

Safety Approvals

- cUL/UL
- CE
- C-Tick

- TUV
- SAA
- Meeting Cal. Prop. 65

Mechanical Characteristics

- Length: 98.5mm (3.88in)
- Width: 55mm (2.17in)

Height: 31.5mm (1.24in) Weight: 243g (8.57oz.)

Output Specifications

Model	DC Output	Load		Efficiency
	Voltage	Min.	Max.	Level*
PSC30U-050	+5V	0A	4.0A	IV.
PSC30U-120	+12V	0A	2.5A	3
PSC30U-240	+24V	0A	1.25A	₩
PSC30U-480	+48V	0A	0.625A	W

See efficiency specification below for more detailed information

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

PSC30U Characteristics

WWW.PHIHONG.COM

Input:

AC Input Voltage Rating

100 to 240V AC

AC Input Voltage Range

90 to 264V AC

AC Input Frequency

47 to 63Hz

Input Current

0.8A (RMS) maximum at 115V AC 0.5A (RMS) maximum at 240V AC

Leakage Current

3.5mA maximum

Inrush Current

60A for 240V AC at maximum load (Cold start at ambient 25°C)

Input Power Saving

0.5W maximum at no load at 115V AC

Output:

Power

20W for 5V

30W for 12V, 24V, 48V

Ripple

5V	50mV		
12V	120mV		
24V	240mV		
48V	480mV		

(Measured after 10 minutes warm up at 25°C with 12-inch twisted pair terminated with a 10uF capacitor and 0.1uF ceramic in parallel.)

Regulation Line & Load

 $\pm 5\%$

Efficiency

Level IV Compliant for all product manufactured after February 2010.

Products manufactured prior to February 2010 are Level IV @115Vac, Level III @230Vac

Hold-up Time

16mS minimum at 120V AC and maximum load

Over-Voltage Protection

By Zener Clamping, Adapter will be shut down

Over-Current Protection

Output equipped with short circuit protection - auto restart

Short-Circuit Protection

Output can be shorted without damage

Environmental:

Temperature

 $\begin{array}{ll} \text{Operation} & 0 \text{ to } +40^{\circ}\text{C} \\ \text{Non-operation} & -30 \text{ to } +85^{\circ}\text{C} \\ \text{Relative Humidity} & 20 \text{ to } 90\% \end{array}$

Emissions

FCC Class B EN55022 Class B

Insulation

Input to Output: DC 500V 7M ohm

Dielectric Withstand (Hi-pot) Test

Input to Output: 1500V AC for 1 min., 10mA

MTBF

50K hours minimum at full load and 25°C

DC Output Connector

2.1 x 5.2 x 10mm Center Positive Standard

DC Cord Length

1850mm (72.8in)

