

ENGLISH

Datasheet

RS Pro DPDT Non-Latching Relay, 24V ac Coil, 10 A

RS Stock No: 450-0419



Product Details

RS Pro DPDT non-latching relay has a coil voltage of 24 V ac. This compact relay withstands currents up to 10 A. It offers connection through silver alloy contacts for added durability.

Features and Benefits

- Contact resistance of 50 mΩ maximum
- Mechanical life: 10 million operations
- Electrical life of 100000 operations





Specifications:

opedifications.	
Application	Power, Control Panel, Sequence Control, Direct Load Switching, Industrial Automation Controllers, Video Projector System, Surge Arrestor
Coil Power	1.2 VA
Coil Resistance	180 Ω
Coil Voltage	24 V ac
Contact Configuration	DPDT
Contact Material	AgSnO2
Depth	21.5 mm
Dimensions	36 x 28 x 21.5 mm
Electrical Life	100000 cycles
Height	36 mm
Isolation Coil To Contact	1500 V ac
Length	28 mm
Life	1000000 cycles (Electrical), 10000000 cycles (Mechanical)
Maximum Operating Temperature	+55°C
Maximum Switching Current (AC)	10 A ac
Maximum Switching Current (DC)	10 A dc
Maximum Switching Power (AC)	2400 VA
Maximum Switching Power (DC)	300 W
Maximum Switching Voltage (AC)	250 V ac
Maximum Switching Voltage (DC)	125 V dc
Minimum Operating Temperature	-45°C
Mounting Type	Socket Mount
Number of Poles	2
Operating Temperature Range	-45 to +55°C
Operating remperature realige	10 10 100 0
Relay Switching Classification	General Purpose Relay

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.



ENGLISH

Standards Met UL E125370, CUR E125370
Terminal Type Plug In