

Isobar 2-Outlet Professional A/V Power Conditioning Center, 10-ft. Cord, 5100 Joules, Low-Profile

MODEL NUMBER: AV2FP



Description

Tripp Lite's AV2FP Professional Isobar Low-Profile Power Conditioning Center for flat screen displays provides ultimate protection (5100 joules) stopping damaging surges/spikes. Filters disruptive EMI/RFI line noise so Digital Displays perform to their full capability! You can see and hear the difference: sharper, crisper deeper, video; helps maintain longer component life spans. Perfect for flat-panel digital displays, Front-screen projection systems and more. High Definition bi-directional 2.2 GHz (gold) coaxial protects against surges /spikes from coming in on the coax input. Network/Ethernet protection with RJ45 covers all 8 pins for matrix switchers and streaming internet content. Premium Isobar surge protection technology. Low-profile all-metal housing installs neatly behind flat-panel displays. 3 diagnostic LEDs report conditions, 2 AC outlets, includes detachable 10-ft. and 18-in. power cords with right-angle plugs, circuit breaker, fail-safe thermal fusing and audible alarm. Built-in mounting bracket. \$100,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only).

Features

- 1-line High Definition bi-directional 2.2 GHz (gold) coaxial surge protection HD-enhanced bandwidth
- 1-Network/Ethernet protection with RJ45 covers all 8 pins for matrix switchers and streaming internet content
- 2 surge / spike protected outlets / includes 2 detachable right angle power cords; 18-in & 10-ft
- 5100 joule surge suppression rating with EMI/RFI line noise filtering helps Digital Displays perform to their full capability! (sharper, crisper video; deeper video; helps maintain longer component life spans)
- ISOBAR Technology filters disruptive EMI/RFI line noise
- 3 Diagnostic LEDs report operational conditions
- Circuit breaker protects against dangerous system overload

Highlights

- 2 surge protected outlets
- 1-line 2.2 GHz (gold) coaxial protection; 1-line Ethernet protection
- ISOBAR technology filters disruptive EMI/RFI line noise
- 5100 joules surge suppression rating
- 2 detachable right-angle power cords; 18-in & 10-ft.
- \$100,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)

Package Includes

- AV2FP Professional Isobar Low-Profile Power Conditioning Center
- Detachable 10-ft. and 18-in power cords, IEC320
- Built-in mounting hardware
- Instruction manual with warranty information



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- All Metal Housing within a low-profile design provides additional EMI / RFI rejection
- Built-in mounting brackets facilitates convenient installation behind any Digital Display
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised
- Audible alarm immediately alerts you to damaged protection circuitry; perfect for when LEDs aren't normally viewed
- TUV tested to UL standards 1449 and 962A
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected components against surge damage - for life!

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) 5-15R
Output (Watts)	1440
Circuit Breaker (amps)	12
Overload Protection	12-amp circuit breaker
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P (detachable cord with IEC C-13 connector)
Input Plug Features	Right-angle plugs
Input Cord Length (ft.)	10
Input Cord Length (m)	3m and 0.5m
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	255000
Right-Angle Plug	0
USER INTERFACE, ALERTS & CONTROLS	
Switches	Circuit breaker
Audible Alarm	Audible alarm
Diagnostic LED Details	3 (protection, grounding, power)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	5100
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Safe Thermal Fusing	yes
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	yes
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	0
Cable (Coax) Protection	1
Network (Ethernet) Protection	1
PHYSICAL	
Unit Dimensions (hwd / in.)	1.50 x 4.50 x 9.25
Unit Weight (lbs.)	1.65
Material of Construction	metal
Included Mounting Accessories	Built-in mounting brackets
Receptacle Color	Black
Color (AC Line Cord)	Black
Outlets Measurement (Center to Center)	45mm
Keyhole Slot Mounting Measurement (Center to Center)	220.49mm
CERTIFICATIONS	
Certifications	Tested to TUV tested to UL standards 1449 and 962A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>