

Eco-Surge 8-Outlet Surge Protector, 8-ft. Cord, 2880 Joules, Tel/Modem/Coax/Ethernet Protection

MODEL NUMBER: AV88SATG



Description

Tripp Lite's AV88SATG offers reliable, GREEN surge technology that protects your computer and peripherals, the environment and your wallet. The ECO-SURGE offers a unique Netbook switch that allows users to select wattage, so ECO-SURGE are the only green surge suppressors compatible with all PCs, Notebooks and Netbooks. Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. AV88SATG offers 8 total outlets, 1-line tel/network data line protection, 1-line 2.2GHz gold coaxial protection, 8 foot cord with space-saving angled plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 2880 joules shields equipment from surges and line noise. Integrated child-safety outlet covers safely seal off unused outlets. Attractive cool gray suppressor housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). PLUG/OUTLETS: Input: NEMA5-15P/Output: 8 NEMA5-15R/8 ft. AC line cord ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle) FORMAT: Corded multi-outlet strip with transformer spaced outlets SUPPRESSION AC: 150V RMS Clamping/2880 joules

Features

- Allows users to switch between GREEN (auto) power save mode and standard (manual) surge protection mode
- 8 total AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- "Master" outlet controls power flow for 1 primary device and up to 5 peripheral devices
- Five "Power Save" outlets cut AC power when not in use--perfect for non-essential peripherals like monitors, printers, scanners, speakers, lamps, etc.
- Two "Always-On" outlets provide continuous power for interminable devices such as modems, routers, external hard drives, cordless phones and fax machines
- 1-line 2.2GHz gold coaxial protection
- 1-line tel/network data line protection
- User-selectable wattage switch accommodates PCs, Netbooks and other Internet research tools
- 2880 joules AC surge suppression shields equipment from the strongest surges and line noise
- Long 8 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection

Highlights

- 8 outlets / 8-ft. cord
- 2880 joule rating
- Auto/Manual switch offers GREEN energy savings or standard protection
- Unique Netbook switch allows user to select wattage
- 1-line 2.2GHz gold coaxial protection
- 1-line tel/network protection
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC protection.

Package Includes

- AV88SATG ECO-SURGE Energy-Saving Surge Suppressor
- 6-ft. tel/network cable
- 6-ft coax cable with gold connectors



- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive black suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OUTPUT	
Output Watt Capacity (Watts)	1800
Frequency Compatibility	60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	Supports 3 large transformer plug accessories without covering remaining outlets
Outlet Details	Includes built-in sliding safety covers
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	8
Input Cord Length (m)	2.4
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	180000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2880
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150



UL1449 Let Through Rating	330 L-G, 400 L-N, 400 N-G
EMI / RFI Filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	Yes
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.04 x 8.66 x 11.41
Shipping Dimensions (hwd / cm)	5.18 x 22.00 x 28.98
Shipping Weight (lbs.)	2.18
Shipping Weight (kg)	0.99
Unit Dimensions (hwd / in.)	1.51 x 4.86 x 9.55
Unit Dimensions (hwd / cm)	3.84 x 12.34 x 24.26
Unit Weight (lbs.)	2
Unit Weight (kg)	0.91
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Color (AC Line Cord)	Black
Metal Case	No
SPECIAL FEATURES	
Green Energy-Saving Features	Power saving auto-shutoff ECO outlets
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance
---	---

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.