


# GBU6A, GBU6B, GBU6D, GBU6G, GBU6J, GBU6K, GBU6M

www.vishay.com


Vishay General Semiconductor


# Glass Passivated Single-Phase Bridge Rectifier



PRIMARY CHARACTERISTICS							
Package	GBU						
I <sub>F(AV)</sub>	6.0 A						
V <sub>RRM</sub>	50 V, 100 V, 200 V, 400 V, 600 V, 800 V, 1000 V						
I <sub>FSM</sub>	175 A						
I <sub>R</sub>	5 μΑ						
V <sub>F</sub> at I <sub>F</sub> = 6.0 A	1.0 V						
T <sub>J</sub> max.	150 °C						
Diode variations	In-Line						

#### **FEATURES**





· High surge current capability

High case dielectric strength of 1500 V<sub>RMS</sub>

• Solder dip 275 °C max. 10 s, per JESD 22-B106

• Material categorization: for definitions of compliance please see





#### **TYPICAL APPLICATIONS**

www.vishay.com/doc?99912

General purpose use in AC/DC bridge full wave rectification for monitor, TV, printer, switching mode power supply, adapter, audio equipment, and home appliances applications.

#### **MECHANICAL DATA**

Case: GBU

Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: As marked on body

**Mounting Torque:** 10 cm-kg (8.8 inches-lbs) max. **Recommended Torque:** 5.7 cm-kg (5 inches-lbs)

MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL	GBU6A	GBU6B	GBU6D	GBU6G	GBU6J	GBU6K	GBU6M	UNIT
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	400	600	800	1000	>
Maximum RMS voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	٧
Maximum DC blocking voltage	$V_{DC}$	50	100	200	400	600	800	1000	٧
Maximum average forward $T_C = 90  ^{\circ}C^{(1)}$		6.0							- А
rectified output current at (fig. 1) $T_A = 40  ^{\circ}\text{C}$ (2)	'F(AV)	3.8							
Peak forward surge current single sine-wave superimposed on rated load	I <sub>FSM</sub>	175			Α				
Rating for fusing (t < 8.3 ms)	l <sup>2</sup> t	127				A <sup>2</sup> s			
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	-55 to +150				°C			

#### **Notes**

<sup>(1)</sup> Unit case mounted on aluminum plate heatsink

<sup>(2)</sup> Units mounted on PCB with 0.5" x 0.5" (12 mm x 12 mm) copper pads and 0.375" (9.5 mm) lead length



# GBU6A, GBU6B, GBU6D, GBU6G, GBU6J, GBU6K, GBU6M

www.vishay.com

# Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)										
PARAMETER	TEST CONDITIONS	SYMBOL	GBU6A	GBU6B	GBU6D	GBU6G	GBU6J	GBU6K	GBU6M	UNIT
Maximum instantaneous forward voltage drop per diode	6.0 A	V <sub>F</sub>				1.0				V
Maximum DC reverse current at rated DC	T <sub>A</sub> = 25 °C	L-				5.0				
blocking voltage per diode	T <sub>A</sub> = 125 °C	I <sub>R</sub>	500							μA
Typical junction capacitance per diode	4 V, 1 MHz	СЈ	68						pF	

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL GBU6A GBU6B GBU6D GBU6G GBU6J GBU6K GBU6M U					UNIT			
Typical thormal registance	R <sub>0JA</sub> (2)	20							°C/W
Typical thermal resistance	R <sub>0</sub> JC (1)(3)	2.5						·	C/VV

#### **Notes**

- (1) Units case mounted on aluminum plate heatsink
- (2) Units mounted in free air, no heatsink on PCB, 0.5" x 0.5" (12 mm x 12 mm) copper pads, 0.375" (9.5 mm) lead length
- (3) Recommended mounting position is to bolt down on heatsink with silicone thermal compound for maximum heat transfer with #6 screws

ORDERING INFORMATION									
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE					
GBU6J-E3/45	3.857	45	20	Tube					
GBU6J-E3/51	3.857	51	250	Paper tray					

### **RATINGS AND CHARACTERISTICS CURVES** (T<sub>A</sub> = 25 °C unless otherwise noted)




Fig. 1 - Derating Curve Output Rectified Current




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current Per Diode



# GBU6A, GBU6B, GBU6D, GBU6G, GBU6J, GBU6K, GBU6M

www.vishay.com

Vishay General Semiconductor




Fig. 3 - Typical Forward Characteristics Per Diode




Fig. 4 - Typical Reverse Leakage Characteristics Per Diode




Fig. 5 - Typical Junction Capacitance Per Diode





Fig. 6 - Typical Transient Thermal Impedance

#### **PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

#### Case Type GBU



Polarity shown on front side of case, positive lead by beveled corner



## **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000