

VGA over Cat5/Cat6 Extender, Wallplate Receiver, 1920x1440 at 60Hz, Up to 1000-ft., TAA

MODEL NUMBER: **B132-100-WP-1**



Description

Tripp Lite's B132-100-WP-1 works with a [B132-002-2](#) or [B132-004-2](#) local transmitter unit to extend a 1920 x 1440 (60Hz) video signal up to 500 ft., or a 1024 x 768 (60Hz) video signal up to 1,000 ft.. 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is required to achieve maximum distance and resolution. For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#). Features built-in Equalization and Gain controls to adjust the video image. RJ45 type wallplate allows you to use standard patch cable, eliminating the need for a 110 punchdown connection. Ideal for digital signage situations, such as retail, schools, churches, etc.

Features

- Works with a B13 or B13 local transmitter unit to extend a 1920 x 1440 (60Hz) video signal up to 500 ft., or a 1024 x 768 (60Hz) video signal up to 1,000 ft.
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#)
- Features built-in Equalization and Gain controls to adjust the video image
- RJ45 type wallplate allows you to use standard patch cable, eliminating the need for a 110 punchdown connection
- Ideal for digital signage situations, such as retail, schools, churches, etc..
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 1 year limited warranty.

Highlights

- Works with a B13 or B13 local transmitter unit to extend a 1920 x 1440 (60Hz) video signal up to 500 ft., or a 1024 x 768 (60Hz) video signal up to 1,000 ft.
- 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's [N022-01K-GY](#) (Cat5) and [N222-01K-GY](#) (Cat6), is required to achieve maximum distance and resolution
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite [P524-01K](#)
- RJ45 type wallplate allows you to use standard patch cable, eliminating the need for a 110 punchdown connection
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- For international use, the B110-INT power supply can be purchased separately; it features plugs for the UK, Europe, and Australia

Package Includes

- Extender remote (Receiver) wallplate
- Mini-Screwdriver for EQ/Gain adjustment
- Wallplate screws
- External Power Supply with



NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.)

- Owner's Manual

Specifications

OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
PHYSICAL	
Shipping Weight (lbs.)	1
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	4.5 x 2.75 x 1
Unit Dimensions (hwd / cm)	11.43 x 6.99 x 2.54
Unit Weight (lbs.)	0.4
Unit Weight (kg)	0.18
Color	White
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	1000
Max 480P Range (ft)	1000
Max 1440 x 900 Range (ft)	500
Max 1080i Range (ft)	500
Max 1080P Range (ft)	500
Max 1920 x 1440 Range (ft)	500
Max 480i Range (ft)	1000
Max 640 x 480 Range (ft)	1000
Max 800 x 600 Range (ft)	1000
Max 1600 x 1200 Range (ft)	500
Max 1920 x 1200 Range (ft)	500
Max 720P Range (ft)	500
CONNECTIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Ports	1
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	HD15 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>