

4-Port Plug-and-Play USB 2.0 over Cat5/Cat6 Extender Hub Kit, Transmitter & Receiver, Hi-Speed USB up to 164 ft. (50 m), TAA

MODEL NUMBER: **B203-104-PNP**



Description

Tripp Lite's [B203-104-PNP](#) 4-Port Plug-and-Play USB 2.0 over Cat5/Cat6 Extender Hub Kit transmits data from your computer to as many as four USB 2.0 peripherals up to 164 ft. (50 m) away. It has plug-and-play functionality, meaning you don't have to install drivers or software. For added convenience, the transmitter has a built-in USB cable for connection to your computer. The USB signals travel between the transmitter and receiver hub over user-supplied Cat5/Cat6 cable. It's a simple, cost-effective solution for connecting your computer to a printer and other USB peripherals that lack network connectivity and are farther than 16 feet away from your computer, which is the distance limitation for USB cables. For example, you can use this kit to connect impact printers to a server in another room. This extender kit is also convenient for making connections in areas without network availability.

By using Cat5/Cat6 cable to carry signals, the [B203-104-PNP](#) extends your installation farther than is possible with standard USB cables. Plus, Cat5/Cat6 cabling is readily available at low cost. For maximum signal integrity, use solid-conductor Cat5/Cat6 UTP cabling, such as Tripp Lite's [N202-series](#). The [B203-104-PNP](#) extender kit can achieve data transfer rates up to 480 Mbps. It's backward compatible with USB 1.1 peripherals, but at USB 1.1 speeds. The [B203-104-PNP](#) works with all major operating systems (Windows and Mac). Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

Long-Distance Data Transfer to 4 Devices—Up to 164 ft. (50 m) from the Source

- Send data to as many as four USB 2.0 devices located up to 164 ft. from the source
- USB signals travel over a single user-supplied Cat5/Cat6 cable
- Includes transmitter with built-in USB-A cable and 4-port receiver hub

Highlights

- Extends USB data transfer up to 164 ft. over Cat5/Cat6 cable
- Includes a transmitter with USB cable and a 4-port receiver hub
- Supports data transfer rates up to 480 Mbps
- Plug-and-play functionality; no software or drivers required
- Works with Windows®, Mac® and Chromebook™ computers

System Requirements

- USB-equipped Windows, Mac or Chromebook computer
- Cat5/Cat6 cable
- Available AC outlet in receiver hub location

Package Includes

- [B203-104-PNP](#) local transmitter with built-in USB cable
- [B203-104-PNP](#) 4-port remote receiver hub
- External Power Supply with NEMA 1-15P Plug for receiver hub (Input: 100-240V, 50/60 Hz, 0.5A; Output: 5V, 2A, 4.5 ft.)
- Owner's Manual



- Supports data transfer rates up to 480 Mbps

Greater Distance over Cat5/Cat6 Cable Provides Greater Flexibility

- Cat5/Cat6 cabling exceeds the 16 ft. distance limitation of USB cables
- Allows connection to devices that lack network connectivity in areas beyond the reach of standard USB cables
- Makes connections in areas without network availability
- Allows source to be in a secure location, separate from peripherals
- Cat5/Cat6 cabling is cost-effective and readily available
- For best results, use solid-conductor Cat5/Cat6 UTP cable, such as Tripp Lite's N202-series cable

Convenient Plug-and-Play Installation

- Plug-and-play functionality; no software or drivers required
- Built-in 1 ft. USB-A cable connects source and transmitter
- User-supplied Cat5/Cat6 cable connects transmitter and receiver hub
- Receiver hub has an external power supply

Widely Compatible

- Compatible with all major operating systems (Windows and Mac)
- Backward compatible with USB 1.1 devices (at USB 1.1 speeds)

TAA-Compliant

- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

MODEL TEXT	
Key Benefit	Send data from a USB-equipped computer to four USB 2.0 peripherals up to 164 ft. away over user-supplied Cat5/Cat6 cable. No software or drivers are required. Kit is useful for devices or areas that lack network conductivity.
OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)



Relative Humidity	20 to 90%
CONNECTIONS	
Ports	4
Side A - Connector 1	USB-A (MALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>