

Universal Power Extension Cord Y Splitter Cable (NEMA 5-15P to 2x IEC-320-C13), 6-ft.

MODEL NUMBER: P006-006-2



Highlights

- Connect two devices to one power outlet
- Plug type - NEMA 5-15P (AC) to 2 x IEC-320-C13 (Device)
- 18AWG SJT, 10A, 125V
- UL Listed

System Requirements

- Computer or other devices with C14 power connectors

Package Includes

- 6-ft. AC Power Splitter Cable, 5-15P to 2 x C13

Description

Tripp Lite's [P006-006-2](#), 6ft Universal AC Power Cord Splitter, allows you to connect two devices with C14 connections, such as computers, to one power outlet. Cuts down on cabling, as well as frees up space on UPS's, Surge Protectors, etc. Main trunk cable measures 47" from 5-15P plug to the splitter housing, 3" housing, and 22" each on the two C13 legs.

Features

- Power two computers or other device from one outlet
- Plug type - NEMA 5-15P (AC) to 2 x IEC-320-C13 (Device)
- 18AWG SJT, 10A, 125V
- 6ft overall length - 47" from 5-15P to split, 22" from split to C13's
- UL Listed

Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black
ENVIRONMENTAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	10 - 85% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	(2) IEC-320-C13
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>