






Compliance with RoHS Directive

ORDERING INFORMATION



Туре	Load current	Load voltage	Input voltage	Part No.
	1A	75 to 264 V AC	5 V DC	AQG12105
			12 V DC	AQG12112
7			24 V DC	AQG12124
Zero-cross	2A	75 to 264 V AC	5 V DC	AQG22105
			12 V DC	AQG22112
			24 V DC	AQG22124
	1A	75 to 264 V AC	5 V DC	AQG12205
			12 V DC	AQG12212
Random			24 V DC	AQG12224
	2A	75 to 264 V AC	5 V DC	AQG22205
			12 V DC	AQG22212
			24 V DC	AQG22224

Standard packing: Carton 20 pcs., Case 500 pcs.

* Sockets for AQ-G solid state relays are also available. Please inquire.

Slim type for PCBs capable of 1 A and 2 A control

FEATURES

 Space saving, Vertical size with a maximum thickness of 4.5 mm.
Mounting space has been reduced to 30% (compared to conventional SSR's) while meeting high density PC board mounting requirements.
Snubber circuit preventing

alfunction

3. Zero-cross type and Random type available

4. High dielectric strength of 3,000V AC (between input and output)

5. Snubber circuit integrated The snubber circuit is integrated to prevent malfunction caused by the rapid rise of voltage on the output side, such as inductive load and current.

AQ-G RELAYS

TYPICAL APPLICATIONS

- Household appliances such as air conditioners, refrigerators and humidifiers
- Healthcare and medical equipment
- Industrial machinery such as NC machines, mounters, injection molders, and robots
- Microcomputer boards
- Amusement and amenity related equipment

SPECIFICATIONS

1. Ratings (at 20°C 68°F, Input voltage ripple: 1% or less)

1) Zero-cross type

Item	Туре		Remarks					
		AQG12105	AQG12112	AQG12124	AQG22105	AQG22112	AQG22124	Remarks
Input side	Input voltage	4 to 6 V DC	9.6 to 14.4 V DC	19.2 to 28.8 V DC	4 to 6 V DC	9.6 to 14.4 V DC	19.2 to 28.8 V DC	
	Input impedance	Approx. 0.3k Ω	Approx. 0.8k Ω	Approx. 1.6k Ω	Approx. 0.3k Ω	Approx. 0.8k Ω	Approx. 1.6k Ω	*1
	Drop-out voltage, min.							
	Reverse voltage							
	Max. load current	1 A AC*2			2 A AC*2			1A: Ta = Max. 40°C 104°F 2A: Ta = Max. 25°C 77°F
	Load voltage							
Load side	Frequency	45 to 65 Hz						
	Non-repetitive surge current	8 A*3			30 A*3			In one cycle at 60 Hz
	Max. "OFF-state" leakage current	1.5 mA (applied 200 V)						at 60 Hz
	Max. "ON-state" voltage drop	1.6 V						at Max. carrying current
	Min. load current	20 mA*4						

2) Random type

14	Туре		Demender					
Item		AQG12205	AQG12212	AQG12224	AQG22205	AQG22212	AQG22224	Remarks
Input side	Input voltage	4 to 6 V DC	9.6 to 14.4 V DC	19.2 to 28.8 V DC	4 to 6 V DC	9.6 to 14.4 V DC	19.2 to 28.8 V DC	
	Input impedance	Approx. 0.3k Ω	Approx. 0.8k Ω	Approx. 1.6k Ω	Approx. 0.3k Ω	Approx. 0.8k Ω	Approx. 1.6k Ω	*1
	Drop-out voltage, min.							
	Reverse voltage							
Load side	Max. load current	1 A AC*2			2 A AC*2			
	Load voltage							
	Frequency							
	Non-repetitive surge current	8 A*3			30 A*3			In one cycle at 60 Hz
	Max. "OFF-state" leakage current		at 60 Hz					
	Max. "ON-state" voltage drop		at Max. carrying current					
	Min. load current	20 mA*4						

Notes: *1. Refer to REFERENCE DATA "3. Input current vs. input voltage characteristics". *2. Refer to REFERENCE DATA "1. Load current vs. ambient temperature". *3. Refer to REFERENCE DATA "2. Non-repetitive surge current vs. carrying time". *4. When the load current is less than the rated minimum load current, please refer to "Cautions for Use of SSR".


2. Characteristics (at 20°C 68°F. Input voltage ripple: 1% or less)

Item	Zero-cross type	Random type	Remarks
Operate time max.	1/2 cycle of voltage sine wave + 1 ms 1 ms		
Release time, max.	1/2 cycle of voltage		
Insulation resistance, min.	10 ⁹ Ω between	at 500 V DC	
Breakdown voltage	3,000 Vrms betwee	for 1 min.	
Vibration resistance	10 to 55 Hz double a	X, Y, Z axes	
Shock resistance	1,000	X, Y, Z axes	
Ambient temperature	-30°C to +80°C	Non-condensing at low temperatures	
Storage temperature	-30°C to +100°C		
Operational method	Zero-cross (Turn-ON and Turn-OFF)	Random turn ON, zero-cross turn OFF	


REFERENCE DATA

AQ-G

1. Load current vs. ambient temperature




3. Input current vs. input voltage characteristics



DIMENSIONS (mm inch)

1.1A type CAD Data







2.-(1) Non-repetitive surge current vs. carrying time

(1A type)

∢

Non-repetitive surge current,

10

\$

F

/

2

0

(1A type)

1.2

1.0

current,


0 pg 0.6

0.4


0.2

0 L

2.-(2) Non-repetitive surge current vs. carrying time (2A type)



4.-(2) Load current vs. ambient temperature characteristics for adjacent mounting (2A type)



The CAD data of the products with a CAD Data mark can be downloaded from: http://panasonic-electric-works.net/ac

100

No. of cycles at 60 Hz

<u>ℓ=1¹5 mm</u>

<u>ℓ=10 mm</u>

60 80

Ambient temperature, °C


4.-(1) Load current vs. ambient temperature

characteristics for adjacent mounting

cent r unting

> 20 40

> > PC board pattern (Bottom view)




Schematic


AC type Output







General tolerance: $\pm 0.2 \pm .008$



Schematic





0 0

Recommended Temperature Controllers



<KT4H Temperature Controller>

Our temperature controller is recommended for use with our Solid State Relays.

Features

- Data can be collected using the RS485 communications interface via a PLC.
- Improved visibility using a negative type LCD and backlight.
- Depth-wise length (chassis dimension) is 56 mm 2.205 inch.

Substitute part numbers

•		
Power supply	Control output	Part No.
100 to 240 V AC	Relay contact	AKT4H111100

*For detailed product information about temperature controllers, please refer to our website: http://panasonic-denko.co.jp/ac/e/fasys/component/temperature_controller/

For Cautions for Use.