

## SmartPro 230V 1.05kVA 650W Line-Interactive Sine Wave UPS, Tower, Network Card Options, USB, DB9, 8 Outlets

MODEL NUMBER: **SMX1050SLT**



### Description

The SMX1050SLT SmartPro 230V 1.05kVA 650W Line-Interactive Sine Wave UPS provides battery backup and AC power protection against blackouts, brownouts, power surges and line noise that can damage electronics or destroy data. Ideal for backing up point-of-sale applications, VoIP systems and small business networks, the SMX1050SLT switches to battery mode in milliseconds to keep your connected equipment running long enough to save files and shut down safely with no data loss.

Featuring eight C13 outlets and a C14 inlet that accepts a user-supplied AC power cord, the SMX1050SLT has an internal battery that provides 20 minutes of support at half load and seven minutes at full load. Front-panel LEDs indicate line power, voltage regulation, load level and battery status. An alarm sounds to indicate power failure or overload.

Automatic voltage regulation (AVR) maintains selectable 220V, 230V or 240V nominal output over an input range of 174V–266V (220V), 182V–278V (230V) or 190V–290V (240V) without using battery power. EMI/RFI noise filtering improves your equipment's performance and prevents damage. A 350-joule surge suppression rating protects your equipment from harmful power surges. With Tripp Lite's downloadable PowerAlert® software, the SMX1050SLT enables safe unattended system shutdown and file saves in case of a prolonged power failure. Adding an optional network management card permits remote management of the UPS, including reboots and activity logs.

### Features

Protects Mission-Critical Equipment

- Provides fully regulated sine wave AC output for point-of-sale applications, VoIP systems and small business networks

### Highlights

- Corrects under- and overvoltages from 182V to 278V (230V)
- 8 C13 outlets
- Front-panel LEDs indicate load, power, voltage and battery statuses
- Network power management and control capability
- 20 min. runtime at half load; 7 min. at full load

### Package Includes

- SMX1050SLT SmartPro 230V 1.05kVA 650W Line-Interactive Sine Wave UPS
- USB cable
- DB9 cable
- (2) IEC-320 C13-to-C14 power cables
- Owner's manual



- Audible alarm signals loss of utility power or overload
- 8 C13 outlets
- C14 inlet accepts user-supplied AC power cord with country-specific plug
- 350-joule surge suppression rating

#### Reliable Battery Backup

- Supports half load up to 20 min. and full load up to 7 min.
- Internal batteries designed for hot-swap field replacement
- Cold-start capability enables turn-on in battery mode during blackouts

#### Automatic Voltage Regulation (AVR)

- Maintains selectable nominal output without using battery power
- Corrects brownouts and overvoltages from 174V–266V (220V), 182V–278V (230V) or 190V–290V (240V)

#### EMI/RFI Line Noise Filtering

- Removes electromagnetic and radio frequency interference that can disrupt or damage equipment's performance

#### LED Indicators

- Front-panel LEDs indicate line power, voltage regulation, load level and battery status

#### Optional Network Management Cards

- Compatible with Tripp Lite UPS management card options [WEBCARDLX](#), [SNMPWEBCARD](#) and [RELAYIOCARD](#)

#### Communication Ports

- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert)

#### Telephone/Network Jacks

- Protect against power surges over telephone/DSL or network Ethernet lines

## Specifications

MODEL TEXT	
Key Benefit	Protects connected mission-critical equipment against damage, downtime and data loss due to blackouts, brownouts, surges and line noise. Ideal solution for point-of-sale applications, VoIP systems and small business networks.



<b>OUTPUT</b>	
Output Volt Amp Capacity (VA)	1050
Output kVA Capacity (kVA)	1.05
Output Watt Capacity (Watts)	650
Nominal Output Voltage(s) Supported	220V; 230V; 240V
Nominal Voltage Details	230V nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Automatic frequency selection
Output Voltage Regulation (Line Mode)	-9%, +5%
Output Voltage Regulation (Battery Mode)	+/- 5%
Output Receptacles	(8) C13
Included Output Power Cables	Includes 2 C13 to C14 output power cables
Hot-Swap PDU options	PDUBHV10 (2U / 8 C13 outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
<b>INPUT</b>	
Rated input current (Maximum Load)	2.8A (230V), 3.0A (220V), 2.7A (240V)
Nominal Input Voltage(s) Supported	220V AC; 230V AC; 240V AC
UPS Input Connection Type	C14 inlet
UPS Input Connection Description	IEC320-C14 input connection accepts a variety of detachable cordsets to match country or site-specific wall receptacles
Input Phase	Single-Phase
<b>BATTERY</b>	
Full Load Runtime (min.)	7 min. (650w)
Half Load Runtime (min.)	20 min. (325w)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 8 hours from 10% to 90% (typical, full load discharge)
Internal UPS Replacement Battery Cartridge	<u>RBC24-SLT</u>
Battery Access	Battery access door
Battery Replacement Description	Hot-swappable, user replaceable batteries



Expandable Runtime	No
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 182 to 278 (230v), 190 to 290 (240v), 174 to 266 (220v)
Overvoltage Correction	Voltage reduction of 12% applies when input is 244 to 278 (230v), 254 to 290 (240v), 232 to 266 (220v)
Undervoltage Correction	Voltage boost of 14% applies when input is 182 to 206 (230v), 190 to 216 (240v), 174 to 198 (220)
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; rear panel protected switches support nominal voltage selection
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Audible alarm indicates power failure and overload conditions
LED Indicators	9 LEDs indicate line power, battery power, AVR, overload and replace battery status - with a 3-LED level meter for load and battery charge level
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	350
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Primary Form Factor	Tower
UPS Power Module Dimensions (hwd, in.)	10.2 x 6.8 x 13.2
UPS Power Module Dimensions (hwd, cm)	25.91 x 17.27 x 33.53
UPS Power Module Weight (lbs.)	36
UPS Power Module Weight (kg)	16.33
UPS Shipping Dimensions (hwd / in.)	14 x 9.8 x 18.5
UPS Shipping Dimensions (hwd / cm)	35.56 x 24.89 x 46.99
Shipping Weight (lbs.)	38.6
Shipping Weight (kg)	17.5
Cooling Method	Fan
UPS Housing Material	Steel
Primary UPS Height (mm)	259



Primary UPS Width (mm)	173
Primary UPS Depth (mm)	335
Shipping Height (mm)	356
Shipping Width (mm)	249
Shipping Depth (mm)	470
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	52
Battery Mode BTU / Hr. (Full Load)	521
AC Mode Efficiency Rating (100% Load)	94%
Operating Elevation (ft.)	Up to 10,000 ft
Audible Noise	Audible Noise < 50 dBA at Front Side 1 Meter
Operating Elevation (m)	Up to 3000m
<b>COMMUNICATIONS</b>	
Communications Interface	USB; DB9 Serial; Slot for SNMP/Web interface
Network Management Cards	SNMPWEBCARD; WEBCARDLX; RELAYIOCARD
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a>
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	4-8 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	174V (220V), 182V (230V) or 190V (240V)
High Voltage Transfer to Battery Power (Setpoint)	266V (220V), 278V (230V) or 290V (240V)
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries



<b>CERTIFICATIONS</b>	
UPS Certifications	CE; Tested to GOST (Russia); Tested to SASO (Saudi Arabia); Meets FCC Part 15 Category B (EMI)
UPS Certification Details	CE / IEC 62040
<b>WARRANTY</b>	
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	2-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>