

INDICATOR LIGHT, 22MM, ROUND, PLASTIC, RED, SMOOTH LENS, WITH HOLDER, LED MODULE, WITH INTEGRATED LED 24V AC/DC, SCREW TERMINAL



Figure similar

product brand name	SIRIUS ACT
Product designation	Commanding and signaling devices
Design of the product	Pilot Light
Manufacturer article number	
• of supplied repeater	3SU1001-6AA20-0AA0
Actuator:	
Product expansion optional Light source	Yes
Color	
• of the actuating element	Red
Material of the actuating element	plastic
Shape of the actuating element	round
Outer diameter of the actuating element	29.45 mm
Front ring:	
Product component front ring	No
Holder:	
Material of the holder	Plastic
Display:	
Number of LED modules	1

General technical data:

Product component <ul style="list-style-type: none">• Light source	Yes
Insulation voltage <ul style="list-style-type: none">• Rated value	320 V
Surge voltage resistance Rated value	4 kV
Protection class IP <ul style="list-style-type: none">• of the terminal	IP66, IP67, IP69(IP69K) IP20
Degree of pollution	3
Shock resistance <ul style="list-style-type: none">• acc. to IEC 60068-2-27• for railway applications acc. to DIN EN 61373	Sinusoidal half-wave 50 g / 11 ms Category 1, Class B
Vibration resistance <ul style="list-style-type: none">• acc. to IEC 60068-2-6• for railway applications acc. to DIN EN 61373	10 ... 500 Hz: 5g Category 1, Class B
Equipment marking <ul style="list-style-type: none">• acc. to DIN EN 61346-2• acc. to DIN EN 81346-2	P P
Relative positive tolerance of the operating voltage	20 %
Relative negative tolerance of the operating voltage	20 %

Auxiliary circuit:

Number of NC contacts <ul style="list-style-type: none">• for auxiliary contacts	0
Number of NO contacts <ul style="list-style-type: none">• for auxiliary contacts	0
Number of CO contacts <ul style="list-style-type: none">• for auxiliary contacts	0

Connections/ Terminals:

Type of electrical connection <ul style="list-style-type: none">• of modules and accessories	Screw-type terminal
Tightening torque <ul style="list-style-type: none">• with screw-type terminals	0.8 ... 0.9 N·m

Lamp:

Type of light source	LED
Color of the light source	red

Ambient conditions:

Ambient temperature <ul style="list-style-type: none">• during operation• during storage	-25 ... +70 °C -40 ... +80 °C
--	----------------------------------

Environmental category during operation acc. to IEC 60721	3K6, 3C3, 3S2, 3M6
---	--------------------

Installation/ mounting/ dimensions:

Mounting type	front panel mounting
• of modules and accessories	Front plate mounting
Height	40 mm
Width	30 mm
Shape of the installation opening	round
Mounting diameter	22 mm
Mounting height	11.8 mm
Installation width	29.5 mm
Installation depth	49.7 mm

Certificates/ approvals:

Declaration of Conformity	other
----------------------------------	--------------



[Bestätigungen](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3SU11026AA201AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/3SU11026AA201AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3SU11026AA201AA0&lang=en



-P
24 V AC/DC



last modified:

13.08.2015