

## Protect It! 8-Outlet Surge Protector, 6-ft. Cord, 2160 Joules, Tel/DSL Protection, Cord Clip

MODEL NUMBER: TLP806TEL



### Highlights

- 8 outlets / 6-ft. cord
- 2160 joule rating
- Modem/fax surge protection
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Package Includes

- TLP806TEL
- 6-ft. telephone cord
- Instruction manual with warranty information

### Description

Tripp Lite's TLP806TEL surge suppressor has 8 outlets, an 6-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Features

- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 2 transformer plugs without blocking outlets covers computers and all peripherals
- Long 6 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- Built-in RJ11 jacks (1 in/1 out) prevent surges from damaging your modem/fax/phone equipment
- Built-in cord management
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive black suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

## Specifications

OUTPUT



|  |  |
|--|--|
| Frequency Compatibility                      | 50 / 60 Hz   |
| Output Receptacles                           | (8) 5-15R  |
| Output (Watts)                               | 1800W  |
| Circuit Breaker (amps)                       | 15   |
| Transformer Accommodation                    | Supports 2 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total |
| Outlet Safety Covers                         | Includes built-in sliding outlet safety covers   |
| Outlet Orientation                           | Single row of 6, plus 2 for transformer accommodation  |
| Right-Angle Outlets                          | 0  |
| <b>INPUT</b>                                 |  |
| Nominal Input Voltage(s) Supported           | 120V AC  |
| Recommended Electrical Service               | 120V (110-125V)  |
| Input Connection Type                        | NEMA 5-15P   |
| Input Plug Features                          | Space-saving right angle input plug  |
| Input Cord Length (ft.)                      | 6  |
| Input Cord Length (m)                        | 1.83   |
| Input Cord Gauge Type                        | 14 gauge, SJT  |
| Voltage Compatibility (VAC)                  | 120  |
| Maximum Surge Amps                           | 144000   |
| Right-Angle Plug                             | 1  |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |  |
| Switches                                     | Combination AC circuit breaker and 2-position red illuminated on/off power switch                                    |
| Diagnostic LED Details                       | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status                            |
| <b>SURGE / NOISE SUPPRESSION</b>             |  |
| AC Suppression Joule Rating                  | 2160   |
| AC Suppression Response Time                 | < 1 ns   |
| Protection Modes                             | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression                                   |
| Clamping Voltage (RMS)                       | 150  |
| UL1449 Let Through Rating                    | 330/400/400  |
| EMI / RFI Filtering                          | Up to 40 dB  |
| <b>DATALINE SURGE SUPPRESSION</b>            |  |
| Telephone/DSL Protection                     | 1  |



|  |   |
|--|---|
| Telephone/DSL Protection Details                     | 1 line  |
| Cable (Coax) Protection                              | 0   |
| Network (Ethernet) Protection                        | 0   |
| <b>PHYSICAL</b>                                      |   |
| Shipping Dimensions (hwd / in.)                      | 13.78 x 5.13 x 2.40   |
| Shipping Dimensions (hwd / cm)                       | 35 x 13.03 x 6.1  |
| Shipping Weight (lbs.)                               | 1.5   |
| Shipping Weight (kg)                                 | .68   |
| Unit Dimensions (hwd / in.)                          | 1.74 x 2.00 x 12.40   |
| Unit Dimensions (hwd / cm)                           | 4.42 x 5.08 x 31.5  |
| Unit Weight (lbs.)                                   | 1.2   |
| Unit Weight (kg)                                     | 0.54  |
| Material of Construction                             | Plastic   |
| Integrated Keyhole Mounting Tabs                     | Keyhole mounting slots enable wall mounting   |
| Receptacle Color                                     | Black   |
| Color (AC Line Cord)                                 | Black   |
| Color  | Black   |
| Outlets Measurement (Center to Center)               | 29mm  |
| Keyhole Slot Mounting Measurement (Center to Center) | Distance between horizontal slots 101.3mm = Distance between vertical slots = 30mm  |
| <b>SPECIAL FEATURES</b>                              |   |
| Additional Information                               | Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line |
| <b>CERTIFICATIONS</b>                                |   |
| UL1449 3rd Edition (AC Suppression)                  | UL1449 3RD EDITION  |
| UL1363 (Power Tap)                                   | UL1363  |
| UL497A (Communications)                              | UL497A  |
| FCC Part 68 (Communications)                         | FCC Part 68   |
| cUL / CSA (Canada)                                   | cUL   |
| Industry Canada (Communications)                     | Industry Canada   |
| Approvals  | Exceeds IEEE 587 category A&B specifications  |
| <b>WARRANTY</b>                                      |   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|   |  |
|---|--|
| Product Warranty Period<br>(Worldwide)                        | Lifetime limited warranty                    |
| Connected Equipment Insurance<br>(U.S., Canada & Puerto Rico) | \$150,000 <u>Ultimate Lifetime Insurance</u> |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>