

230 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 3/8 16 X 1 3/8" stud
- Load: (1) 3/8 16 X 1 3/8" stud

Electrical Ratings

- 230 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- SCCR of 10,000 A (default for terminal blocks).
- Factory & Field Wiring

Agency Compliance

- UR UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA certifed to C22.2 No. 158, File No. LR19766

Material Information

- Insulator base:
 - Phenolic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 150°C (UL RTI)
- Connector: copper, tin plated
- Threaded stud: steel, zinc plated
- Hex nut: brass, nickel plated (1 supplied per stud)
- RoHS compliant



Product Data Sheet

143X563 Replace "x" with 1, 2, or 3 for number of poles

Power Terminal Block

A Regal Brand



www.regalbeloit.com

marathon[®] Special Products

Termination Specifications

Line & load Side	Termination Type	Torque	Stud Length	Maximum Lug/Bar Width
	Listed lugs on	21.7 N⋅m	1 3/16″	1.16"
	3/8 - 16 studs	(192 lbf⋅in)	(30mm)	(30mm)

• For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.

• Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.

Installation & Accessories

- Mounting (Panel):
 - For use with #10 fastener.
 - Mounting torque to be determined in end use application not to exceed 30 lbf-in (3.4 N·m).
- Covers:
 - Flat covers available upon request
 - Catalog Number: CC 143x (replace "x" with number of poles)
 - Covers are clear polycarbonate
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.



Drawing

