



# SPECIFICATION SHEET

## 22-760G



### KUT-GARD® POLYESTER OVER DYNEEMA® / SILICA / STAINLESS STEEL CORE ANTIMICROBIAL GLOVE - MEDIUM WEIGHT

- Yarns constructed of flexible steel core strands offer exceptional cut and slash resistance
- Seamless construction provides comfort, fit and dexterity
- Made from component materials that comply with Federal Regulations for food contact 21CFR, 170-199
- Features patented NSF/ANSI Standard 51 Conformant and FDA & EPA Antimicrobial Fibers. Inhibits the growth of microorganisms such as bacteria and mold that come in contact with the fiber up to 99.9%
- Available with different colored cuffs to distinguish between areas of use
- CFIA Approved

### APPLICATIONS

- Food Service applications
- Food Processing
- Glass and metal handling

### CARE INSTRUCTIONS

Machine wash in warm water with Detergent. Rinse well and spinextract using low speed. Tumble dry on Low to Medium heat setting. Temperature settings not to exceed 65°C. Can be Dry-Cleaned.

### TECHNICAL DATA

MATERIAL	Dyneema®, stainless steel and other synthetic fibers
CONSTRUCTION	10 gauge seamless knit reversible
COLOR	■ Gray
CUFF STYLE	Knitted elasticized wrist
SIZES	XS - XL
PACKAGING	24 each per case
CASE	12.0" x 6.0" x 6.0" / 30.5cm x 15.3cm x 15.3cm
CASE WEIGHT	1.4 lbs / 0.6 kg
COO	USA
HARM CODE	6116.93.8800US

### CUT RESISTANCE PROPERTIES

- Method ASTM F1790-04
- 4000 ± 400 grams
- ANSI/ISEA 105-2000 Level 5 Cut Resistance

### BARCODES

ITEM	EACH	DOZEN	CASE
■ 22-760G/XL	---	---	---
■ 22-760G/L	---	---	---
■ 22-760G/M	---	---	---
■ 22-760G/S	---	---	---
■ 22-760G/XS	---	---	---



### DIMENSIONS (in/cm)

	XS	S	M	L	XL
<b>A</b>	8.0 / 20.3	8.5 / 21.6	24.1 / 9.5	10.5 / 26.7	11.0 / 27.9
<b>B</b>	3.75 / 9.5	4.0 / 10.2	4.5 / 11.4	4.5 / 11.4	4.5 / 11
<b>H</b>	■ Black	■ Yellow	■ Blue	□ White	■ Green

