



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. ALL DIMENSIONAL TOLERANCES ± 1.0 mm.
2. INDUCTIVITY: 257 microHenry
3. Q = 55.2
4. Q DISTANCE 1.3 mm = 27.7

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
1.				DRFT RDS		DATE 04/29/04	
2.				APVD		SCALE 1=1.0	
3.		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DESCRIPTION			
4.				BI 3-Q08-ES/S1027 0.2M			
MATERIAL		CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT		IDENTIFICATION NO.	
FINISH				INCH [MILLIMETER]		M1044691	
A DRAWING RELEASE		RDS 04/29/04		DO NOT SCALE THIS DRAWING		FILE: M1044691	
REV DESCRIPTION		BY DATE ECO NO.				SHEET 1 OF 1	