

280-ML5151 Specification Sheet

COMFORT PLUS 5151 HARD HAT - TYPE I

PRODUCT DESCRIPTION:

Comfort Plus 5151 Hard Hat, ratchet adjustment, 6-pt polyester strap suspension, ANSI Z89.1 Type 1, Class G, available in white, yellow, green, blue, red or orange.

- Conforms to ANSI Z89.1-2009 Type I Class G;
- High-density polyethylene (HDPE) shell dissipates impact energy;
- Shock-absorbing 6-point suspension with adjustable polyester straps;
- · Ratchet suspension that pivots for optimum adjustment;
- Brushed nylon backed foam sweatband;
- Universal slots to accept various accessories;
- · Packed ready-to-wear with no assembly required;

Applications:

Provide protection from falling debris, low hanging objects and electrical hazards. The use of ANSI compliant head protection is required by OSHA and helps workers avoid serious injury.

TECHNICAL DATA:

Material:

Shell: HDPE; Webbing: LDPE Strap; Harness: LDPE Harness Clips, Polyester Web Straps. Comes with Brushed Nylon Backed Foam Sweatband Color: 10 - White 20 - Yellow 39 - Pink 30 - Green 60 - Red 50 - Blue 80 - Orange

Available Sizes: Adjustable Packaging: 1 per polybag; 35 per case Case Dimensions: (cm) - 76 x 58 x 43 / (in) - 30 x 23 x 17 Case Weight: 36 lbs / 16.3 kg Country of Origin/Harmonization Code: UAE/6506.10.6075

Laundering Instructions:

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

BARCODE #	EACH	CASE
280-ML5151-10	5038428119856	5038428811088
280-ML5151-20	5038428119863	5038428811095
280-ML5151-30	5038428119870	5038428811125
280-ML5151-39	5038428143639	5038428812344
280-ML5151-50	5038428119887	5038428811101
280-ML5151-60	5038428119894	5038428811118
280-ML5151-80	5038428119900	5038428811132



SIZE & WEIGHT:

Size available - One size		
(cm)	53 - 61	
(in)	20 ⁷ / ₈ – 23 ⁷ / ₈	
Hat size	6 5⁄8 - 7 5⁄8	
Weight	14.1 ounces / 400 grams	

CONFORMITY:

Complies with ANSI Z89.1-2009 Type I, Class G and EN 397

INSTRUCTIONS FOR USE:

Fit helmet on head and fasten strap to ensure correct fit. For adequate protection this helmet must be worn with the peak facing forward and be adjusted to the size of the users head.

LIMITATIONS OF USE:

Protection will only be offered if the helmet is fitted correctly. Any Helmet subjected to severe impact should be replaced immediately. Do not apply paint, solvents, adhesives or self-adhesive labels, except in accordance with instructions from the manufacturer. The harness, when in contact with the skin may cause allergic reactions to susceptible individuals. If this occurs leave the hazard area, remove the helmet and seek medical advice. The attention of users is also drawn to the dangers of modifying or removing any of the original component parts, other than as recommended by the manufacturer.

This document is the property of PIP and the information contained herein is proprietary to PIP.

Protective Industrial Products | 26 Computer Drive East | Albany, NY 12205

Phone: 518-861-0133 | Toll free: 800-262-5755 | Fax: 518-861-0144 | www.pipusa.com | sales@pipusa.com