

For more Information
please call

1-800-Belden1



General Description:

18 AWG solid bare copper-covered steel conductor, foam FEP insulation, Duobond® IV Quad Shield (100% coverage), fluorocopolymer Jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BCCS - Bare Copper Covered Steel	.040

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FFEP - Foam Fluorinated Ethylene Propylene	.170

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	60
3	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
4		Braid	AL - Aluminum	40

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVDF - Fluorocopolymer

Overall Cable

Overall Nominal Diameter: 0.274 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +150°C

Non-UL Temperature Rating: 150°C

Bulk Cable Weight: 43 lbs/1000 ft.

Max. Recommended Pulling Tension: 104 lbs.

Min. Bend Radius/Minor Axis: 2.750 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

RG Type: 6/U

Flame Test

3093A Coax - ControlNet™ Quad Shielded Coax

UL Flame Test: NF-PA 262

Suitability

Suitability - Outdoor: Yes

Suitability - Burial: Yes

Plenum/Non-Plenum

Plenum (Y/N): Yes

Non-Plenum Number: 3092A

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/ft)
.093

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
16.3

Nominal Velocity of Propagation:

VP (%)
82

Nominal Delay:

Delay (ns/ft)
1.28

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
28.0

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
3.6

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.36
2	.38
5	.50
10	.65
20	.95
50	1.50
100	2.12
200	2.99
300	3.66
400	4.23

Minimum Structural Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
		5	50	23

Notes (Overall)

Notes: Blue available as standard in 1000-ft put-up only. Suitable for Outdoor and Direct Burial applications.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
3093A X7E1000	1,000 FT	40.000 LB	BLUE X7E	C	#18 FFEP DBSH SLF
3093A 0101000	1,000 FT	40.000 LB	BLACK	C	#18 FFEP DBSH SLF
3093A 0102000	2,000 FT	80.000 LB	BLACK	C N	#18 FFEP DBSH SLF
3093A 0102500	2,500 FT	95.000 LB	BLACK	C N	#18 FFEP DBSH SLF
3093A 0105000	5,000 FT	195.000 LB	BLACK	C Z	#18 FFEP DBSH SLF

Notes:

C = CRATE REEL PUT-UP.

N = FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

3093A Coax - ControlNet™ Quad Shielded Coax

Revision Number: 2 Revision Date: 09-04-2013

© 2015 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.