# **SIEMENS**

#### Data sheet

### 6GK5205-3BD00-2TB2

#### **Product type designation** Product description

## SCALANCE XB205-3

Preset for Ethernet/IP mode!

SCALANCE XB205-3 MANAGEABLE LAYER 2 IE-SWITCH 5X 10/100 MBITS/S RJ45 PORTS 3X MM FO SC-PORT 1X CONSOLE PORT DIAGNOSTICS LED REDUNDANT POWER SUPPLY TEMP. RANGE 0 DGR C UP TO +60 DGR C; DIN-RAIL MOUNTING ETHERNET/IP CONFORMAL DEFAULT ETHERNET/IP



Transmission rate	
Transfer rate	10 Mbit/s, 100 Mbit/s
Interfaces / for communication / integrated	
Number of electrical connections	
<ul> <li>for network components or terminal equipment</li> </ul>	5
Number of 100 Mbit/s SC ports	
• for multimode	3
Interfaces / others	
Number of electrical connections	
<ul> <li>for operator console</li> </ul>	1
<ul> <li>for management purposes</li> </ul>	1
• for power supply	1
<ul> <li>for redundant voltage supply</li> </ul>	1
Type of electrical connection	
<ul> <li>for operator console</li> </ul>	RJ11 port
<ul> <li>for management purposes</li> </ul>	RJ45 port

• for power supply

6-pole terminal block

• for power suppry		
Supply voltage, current consumption, power loss		
Type of voltage / of the supply voltage	DC	
Supply voltage		
• external	24 V	
• external	19.2 28.8 V	
Product component / fusing at power supply input	Yes	
Consumed current / maximum	0.3 A	
Permitted ambient conditions		
Ambient temperature		
• during operation	0 60 °C	
<ul> <li>during storage</li> </ul>	-40 +70 °C	
• during transport	-40 +70 °C	
Relative humidity		
<ul> <li>at 25 °C / without condensation / during</li> </ul>	96 %	
operation / maximum		
Protection class IP	IP20	
Design, dimensions and weight		
Design	compact	
Width	80 mm	
Height	117 mm	
Depth	109 mm	
Net weight	0.35 kg	
Material / of the enclosure	Plastic	
Mounting type		
<ul> <li>35 mm DIN rail mounting</li> </ul>	Yes	
• wall mounting	No	
<ul> <li>S7-300 rail mounting</li> </ul>	No	
• S7-1500 rail mounting	No	
Product properties, functions, components / general		
Cascading in the case of a redundant ring / at	50	
reconfiguration time of <\~0.3\~s		
Cascading in cases of star topology	any (depending only on signal propagation time)	
Product functions / management, configuration		
Product function		
• CLI	Yes	
<ul> <li>web-based management</li> </ul>	Yes	
MIB support	Yes	
• TRAPs via email	Yes	
Configuration with STEP 7	Yes	
RMON	Yes	

• De devine de la	Yes
Port mirroring	
multiport mirroring	No
• CoS	Yes
• with IRT / PROFINET IO switch	No
PROFINET IO diagnosis	Yes
• switch-managed	Yes
Telegram length / for Ethernet / maximum	1522 byte
Protocol / is supported	Vez
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
EtherNet/IP	Yes
<ul> <li>IGMP (snooping/querier)</li> </ul>	Yes
Identification & maintenance function	
<ul> <li>I&amp;M0 - device-specific information</li> </ul>	Yes
<ul> <li>I&amp;M1 – higher-level designation/location</li> </ul>	Yes
designation	
Protocol / is supported	
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
Product functions / Diagnosis	
Product function	
Port diagnostics	Yes
Statistics Packet Size	Yes
<ul> <li>Statistics packet type</li> </ul>	Yes
Error statistics	Yes
• SysLog	Yes
<ul> <li>loopback diagnostics</li> </ul>	Yes
Product functions / VLAN	
Product function	
<ul> <li>VLAN - port based</li> </ul>	Yes
<ul> <li>VLAN - protocol-based</li> </ul>	No
• VLAN - IP-based	No
VLAN dynamic	No

Product functions / DHCP	
Product function	
DHCP client	Yes
Product functions / Redundancy	
Product function	
<ul> <li>Ring redundancy</li> </ul>	Yes
<ul> <li>High Speed Redundancy Protocol (HRP)</li> </ul>	Yes
<ul> <li>high speed redundancy protocol (HRP) with redundancy manager</li> </ul>	Yes
<ul> <li>high speed redundancy protocol (HRP) with standby redundancy</li> </ul>	No
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
<ul> <li>media redundancy protocol (MRP) with redundancy manager</li> </ul>	Yes
<ul> <li>redundancy procedure STP</li> </ul>	Yes
<ul> <li>redundancy procedure RSTP</li> </ul>	Yes
<ul> <li>redundancy procedure MSTP</li> </ul>	Yes
<ul> <li>Parallel Redundancy Protocol (PRP)/operation in the PRP-network</li> </ul>	No
<ul> <li>Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)</li> </ul>	No
Passive listening	Yes
Product functions / Security	
Product function	
• IEEE 802.1x (radius)	Yes
<ul> <li>Broadcast/Multicast/Unicast Limiter</li> </ul>	Yes
<ul> <li>broadcast blocking</li> </ul>	Yes
Protocol / is supported	
• SSH	Yes
Product functions / Time	
Product function	
SICLOCK support	Yes
Protocol / is supported	
• NTP	Yes
• SNTP	Yes
Standards, specifications, approvals	
Standard	
• for FM	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T5

<ul> <li>for hazardous zone</li> </ul>	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul> <li>for safety / from CSA and UL</li> </ul>	UL 60950-1, CSA C22.2 No. 60950-2
<ul> <li>for hazardous zone / from CSA and UL</li> </ul>	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T5
• for emitted interference	EN 61000-6-4 (Class A)
• for interference immunity	EN 61000-6-3
Certificate of suitability / CE marking	Yes
Certificate of suitability	EN 61000-6-2, EN 61000-6-5
• C-Tick	Yes
<ul> <li>Railway application in accordance with EN 50155</li> </ul>	No
<ul> <li>Railway application in accordance with EN 50124-1</li> </ul>	No
<ul> <li>KC approval</li> </ul>	Yes
Further Information / Internet Links	
Internet-Link	
<ul> <li>to website: Selector SIMATIC NET SELECTION TOOL</li> </ul>	http://www.siemens.com/snst
<ul> <li>to website: Industrial communication</li> </ul>	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
<ul> <li>to website: Information and Download Center</li> </ul>	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
<ul> <li>to website: CAx Download Manager</li> </ul>	http://www.siemens.com/cax
<ul> <li>to website: Industry Online Support</li> </ul>	https://support.industry.siemens.com
Security information	
Security information	Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action(e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit http://www.siemens.com/industrialsecurity. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information.siemens.com. (V3.4)
last modified:	07/07/2016