

Datasheet

ENGLISH

Stock No: 119-160

RS ProCT Series Uninsulated Tin Plated Tubular Ring Terminal, M6 Stud Size, 6 mm²



Product Details

R\$ Pro Ring Tube Crimp Terminals

From RS Pro, a range of heavy duty copper tube ring terminals manufactured from a pure grade copper base to BS2871 and electro-tin plated to BS1872,1984. These HD copper tube ring crimp terminals are for use on multi-stranded cables and are available with a flared or a chamfered entry (see stock numbers 841-7598 and 841-7608) and in a variety of sizes.

For suitable crimp tools please see stock numbers 241-4710, 445-611 and 445-885

RS Tube Terminals - Uninsulated Terminals & Kits

Tube Terminals

Heavy duty tube terminals and butt splices for terminating cables in the 6mm² to 150mm² size range. The terminals are available with different bolt hole diameters. Both ring terminals and butt splices are manufactured from tinned copper tube with a flared cable entry to ease termination (Excepting 6mm² size). Rated to 150°C.



ENGLISH

Specifications:

| Wire Size | 6 mm² |
|---------------------|-------------|
| Stud Size | M6 |
| Inner Ring Diameter | 6.4mm |
| Insulation | Uninsulated |
| Contact Material | Copper |
| Shrouded | Unshrouded |
| Contact Plating | Tin |
| Series | CT |
| Overall Length | 23mm |