



# Retra-drive Screwdrivers







## RETRA-DRIVE SCREWDRIVERS

- 15 in 1 Interchangeable Screwdriver
- 15 in 1 Interchangeable HVAC Screwdriver
- Interchangeable Tamper Proof Screwdriver
- Ratcheting Interchangeable Screwdriver



• Palm saver cap

• Patented pull out retracting cartridge design

• Handle is made from ABS resin

• Easy guide collar

• Alloy steel shaft

• Diameter 1-3/8" (35mm)





# RETRA-DRIVE SCREWDRIVERS

**790-4700**

## 15 IN 1 INTERCHANGEABLE SCREWDRIVER

- All purpose bit load driver loaded with 7 double end professional quality bits
- Magnetic bit holder. End of Shaft is a 1/4" hex nut driver
- Retractable Bit Cartridge - Makes it easy to find, store and change bits
- Specially designed Palm Saver Cap prevents blisters in the palm of your hand. Cap does not turn as you push on the cap and turn the handle
- Easy Guide Collar provides greater control by maintaining full contact between the bit and the screw
- Specially Engineered ABS resin handle
- Industrial grade S2 modified Steel bits with Rockwell hardness 58 - 62
- Phillips 0-3, Pozi 1-2, Slotted 4-6, Hex 1/8" -5/32", Torx 10-30



CODE NO	HxW / mm	kg
790-4700	225 x 40	0.23



**790-4704**

## 15 IN 1 INTERCHANGEABLE HVAC SCREWDRIVER

- 14 bit tips featuring valve stem bit, Square Awl Reamer Bit and Double LOK Phillips #2 combo bit (which can be used in any 1/4" quick change chuck)
- Magnetic bit holder. End of Shaft is a 1/4" hex nut driver
- Retractable Bit Cartridge - Makes it easy to find, store and change bits
- Specially designed Palm Saver Cap prevents blisters in the palm of your hand. Cap does not turn as you push on the cap and turn the handle
- Easy Guide Collar provides greater control by maintaining full contact between the bit and the screw
- Specially Engineered ABS resin handle
- Industrial grade S2 modified Steel bits with Rockwell hardness 58 - 62
- Phillips 0-3, Double ended phillips 2-2, Slotted 3-6, Slotted 5.5 valve stem, Square Awl



CODE NO	HxW / mm	kg
790-4704	225 x 40	0.23






# RETRA-DRIVE SCREWDRIVERS

**790-4713**

## INTERCHANGEABLE TAMPER PROOF SCREWDRIVER

- Must for all commercial/industrial tradesmen i.e.electricians, locksmiths, telephone technicians, maintenance personnel, etc
- Magnetic bit holder. End of Shaft is a 1/4" hex nut driver
- Retractable Bit Cartridge - Makes it easy to find, store and change bits
- Specially designed Palm Saver Cap prevents blisters in the palm of your hand. Cap does not turn as you push on the cap and turn the handle
- Easy Guide Collar provides greater control by maintaining full contact between the bit and the screw
- Specially Engineered ABS resin handle
- Industrial grade S2 modified Steel bits with Rockwell hardness 58 - 62
- Hex pin 1/8", 9/64", 5/32", 3/16", Spanner6-12, Torq pin 10-30



CODE NO	HxW / mm	kg
790-4713	225 x 40	0.23



**790-4716**

## RATCHETING INTERCHANGEABLE SCREWDRIVER

- Features ZAD 8 Zinc Alloy SOLID-CORE ratchet that delivers over 25 Nm of torque strength. Precision 28 Tooth ratchet design makes driving fasteners faster and easier
- Magnetic bit holder. End of Shaft is a 1/4" hex nut driver
- Retractable Bit Cartridge - Makes it easy to find, store and change bits
- Specially designed Palm Saver Cap prevents blisters in the palm of your hand. Cap does not turn as you push on the cap and turn the handle
- Easy Guide Collar provides greater control by maintaining full contact between the bit and the screw
- Specially Engineered ABS resin handle
- Industrial grade S2 modified Steel bits with Rockwell hardness 58 - 62
- Phillips 0-3, Pozi 1-2, Slotted 4-6, Torx 10-25



CODE NO	HxW / mm	kg
790-4716	225 x 40	0.23

