



P.V.C Grommet kit


RS stock no. 541-056
(containing 470 grommets in 18 sizes)



Grommet material PVC grade VX329

Normal shore hardness 55°

Maximum constant working temperature 70°



Panel hole dia.	4.8	6.4	6.4	7.9	9.6	9.6
Bore dia.	3.2	4.0	4.8	5.6	4.8	5.4
Outside dia.	7.9	9.6	9.6	10.6	13.8	13.8
Overall thickness	6.4	6.2	7.1	6.4	5.4	6.5
Panel hole dia.	10.7	10.7	12.7	12.7	12.7	14.3
Bore dia.	6.4	6.0	4.8	7.9	9.6	11.1
Outside dia.	14.3	14.3	19.0	19.0	16.7	19.0
Overall thickness	8.6	14.3	7.9	8.0	7.1	7.9
Panel hole dia	15.9	15.4	17.5	19.0	22.2	25.4
Bore dia.	4.8	10.5	7.9	12.0	15.9	19.0
Outside dia.	20.6	18.5	27.0	25.4	27.0	31.6
Overall thickness	7.9	9.8	6.4	7.9	7.9	8.1

All dimensions in millimetres