



**Cable and Fibre Type**

Grade of the cable: LSZH

Fibre type (ISO/IEC 11801-2002)		Outer Sheath Colour
62.5/125	OM1	Orange
50/125	OM2	Orange
50/125	OM3	Purple
09/125	OS1	Yellow

**Connector:** SC Clips shall be mounted to the connector to make it duplex.

**Optical Performance (IEC 61300-3-4):**

**Multimode (@ 1300nm)**

Max. IL - 0.30dB Typical: 0.20dB

**Singlemode (@1310nm and/or 1550nm)**

Max. IL - 0.30dB Typical: 0.20dB Return Loss: >50dB

**RoHS Compliant**

**Coiling Diameter:** Coiling Diameter of the patchcord shall be greater than 200mm

**Packing:** Each product shall be individually bagged and identified with a unique number printed on an ID label affixed to the product. Also, each product will be supplied with a Test Certificate.

Id No.	Description	Ea
1.	ST Connector	2
2.	SC Connector	2
3.	SC & ST Boots	4
4.	Identification Label	1
5.	2.8mm Duplex Cable (L m)	1
6.	Black Tape	2

REV	DESCRIPTION	DATE	DRN	APD	REV	DESCRIPTION (REVISION RECORD)	DATE	DRN	APD

  

FINISH	SCALE	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PART NO.	QTY/REV. NO.	CHD
-	Not to Scale	0 P.C. ± 0.04	<b>ST-SC Duplex PATCHCORD</b>	01	
		1 P.C. ± 0.04			
		2 P.C. ± 0.04			
		3 P.C. ± 0.04			
		4 P.C. ± 0.04			
		2 ANG. ± 0.04			

  

ALL DIMENSIONS IN MM					
----------------------	--	--	--	--	--

  

--	--	--	--	--	--

  

--	--	--	--	--	--

  

--	--	--	--	--	--

  

--	--	--	--	--	--

  

--	--	--	--	--	--