

Energy Management

Compact Power Transducer

Type CPT-DIN "Advanced version"

CARLO GAVAZZI



- One digital output and RS485 communication port (2 wires only)
- 16 freely configurable alarms with OR/AND logic linkable to up to 2 digital outputs
- RS422/485/RS232 communication port (MODBUS-RTU), iFIX SCADA compatibility

Product Description

3-phase compact power transducer. Particularly recommended for the measurement of the main electrical variables also on board of machines.

Housing for DIN-rail mount-

ing, with up to 3 analogue outputs, or RS485 communication port or alarm outputs or "Dupline" bus. Parameters programmable by means of CptASoft.

- Class 1 (kWh), Class 2 (kvarh)
- Accuracy ± 0.5 F.S. (current/voltage)
- Compact power transducer
- Instantaneous variables data format: 4 DGT
- Energies data format: 8+1 DGT
- System variables and phase measurements: V_{LL} , V_{LN} , A , A_{max} , A_n , A_{dmd} , $A_{dmd\ max}$, VA , VA_{dmd} , $VA_{dmd\ max}$, W , W_{dmd} , $W_{dmd\ max}$, W_{L1} , W_{L2} , W_{L3} max, var, PF, PF_{L1} , PF_{L2} , PF_{L3} min, Hz, ASY
- Four quadrant power measurement
- Energy measurements: total and partial kWh and kvarh (according to EN62053-21 and EN62053-23)
- Hour counter (5+2 DGT)
- TRMS meas. of distorted sine waves (voltages/currents)
- Universal power supply: 90 to 260 VAC/DC, 18 to 60 VAC/DC
- Dimensions: 45x83.5x98.5mm
- Voltage asymmetry, phase sequence, phase loss control
- Up to 3 analogue outputs (20mA or 10VDC)
- 2 digital outputs

How to order

CPT-DIN AV5 3 H A3 AX



How to order CptASoft-kit

CptASoft: software to program the working parameters of the transducer and to read the energies and the instantaneous variables. The kit includes the communication cable.

Type Selection

Range codes	System	Outputs	Options
AV5: 400/690V _{LL} /1/5(6)AAC V _{L-N} : 185 V to 460 V V _{LL} : 320 V to 800 V	3 : 1-2-3-phase, balanced/ unbalanced load, with or without neutral	R2: 2-relay outputs O2: 2-open collector outputs A1: 1-analogue output: 0/4 to 20mA DC A3: 3-analogue outputs: 0/4 to 20mA DC V1: 1-analogue output: 0 to 10V DC V3: 3-analogue outputs: 0 to 10V DC S1: RS485/RS422 port S2: RS232 port DB: Dupline bus	AX: advanced functions
AV6: 120/208V _{LL} /1/5(6)AAC V _{L-N} : 45 V to 145 V V _{LL} : 78 V to 250 V Phase current: 0.01A to 6A Neutral current: 0.05A to 6A	1 : 1-3-phase, balanced load (*)	(*) Note: the 3-phase balanced load measurement requires the connection of the neutral according to fig. 15 and 16 in the final part of this document.	Power supply L: 18 to 60 VAC/VDC H: 90 to 260 VAC/VDC

Input specifications

Rated inputs	System type: 3 3 (internal current transformers) 4	Neutral current Phase-phase voltage Phase-neutral voltage Active and Apparent power, Reactive power Range accuracy: 0.05In to Imax	$\pm(2\%RDG+3DGT)$ $\pm(0.5\%RDG+2DGT)$ $\pm(0.5\%RDG+2DGT)$ $\pm(1.5\%RDG+3DGT)$ $\pm(3\%RDG+3DGT)$
Current Voltage	System type: 1 1 (internal CT) 2	Current Neutral current Phase-phase voltage Phase-neutral voltage Active and Apparent power,	$\pm(0.5\%RDG+2DGT)$ $\pm(1\%RDG+3DGT)$ $\pm(0.5\%RDG+2DGT)$ $\pm(0.5\%RDG+2DGT)$ $\pm(1\%RDG+3DGT)$
Current Voltage	Imax: 6A, Vmax: 400V _{LN} (690V _{LL}) In: 5A, Vn: 230V _{LN} (400V _{LL}) CT: 1, VT (PT): 1 $\pm(0.5\%FS)$ or $\pm(1\%RDG+2DGT)$		
Accuracy (RS485) (@25°C $\pm 5^\circ\text{C}$, R.H. $\leq 60\%$)			

Input specifications (cont.)

Reactive power	$\pm(2\% \text{RDG} + 3\text{DGT})$	Hourcounter	5+2 DGT, max indication 9 999 9.99
Active energy	Class 2 according to EN62053-21 (I start up: 10mA)		
Reactive energy	Class 3 according to EN62053-23 (I start up: 10mA)		
Frequency	$\pm 0.1\text{Hz}$ (48 to 62Hz)		
Additional errors		Measurements	
Humidity	$\leq 0.3\%$ FS, 60% to 90% RH	Type	Current, voltage, power, power factor, frequency
Frequency	$\leq 0.3\%$ FS (45 to 48Hz and 62 to 65Hz)	Coupling type	TRMS measurement of distorted waves.
		Crest factor	Direct < 3 , max 10A peak
Temperature drift	$\leq 200\text{ppm}/^\circ\text{C}$	Input impedance	1.6 M Ω $\pm 5\%$
Sampling rate	1600 samples/s @ 50Hz 1900 samples/s @ 60Hz	400/690V _{L-L} (AV5) 120/208V _{L-L} (AV6)	1.6 M Ω $\pm 5\%$
Measurement refresh time	200ms	Current	$\leq 0.01\Omega$
Measurement format	(serial communication)	Frequency	45 to 65 Hz
Instantaneous variables	4 DGT, max indication 9999	Overload protection	(max values)
Energies	8+1 DGT, max indication 999 999 99.9	Continuos voltage/current	AV5: 460V _{LN} /800V _{LL} /6A AV6: 145V _{LN} /250V _{LL} /6A
		For 500ms: voltage/current	AV5: 800V _{LN} /1380V _{LL} /36A AV6: 240V _{LN} /416V _{LL} /36A

Output Specifications

Analogue Outputs			
Number of outputs	Up to 3	Set-point adjustment	From 0 to 100% of the retransmitted scale
Accuracy (@25°C $\pm 5^\circ\text{C}$, R.H. $\leq 60\%$)	$\pm 0.3\%$ FS	Hysteresis	from 0 to full scale
Range	0 to 20mA or 0 to 10 VDC	On-time delay	0 to 255s
Scaling factor:	Programmable within the whole range of retransmission; it allows the retransmission management of all values from: 0 and 20 mA, 0 and 10VDC	Output status	Selectable; normally de-energized and normally energized
	≤ 400 ms typical (filter excluded)	Min. response time	≤ 400 ms, filters excluded and with alarm delay: "0s"
Response time	$\leq 1\%$, according to IEC 60688-1, EN 60688-1	Note	The 2 digital outputs can also work as one pulse output and one alarm output.
Ripple	≤ 500 ppm/ $^\circ\text{C}$		
Total temperature drift	≤ 350 Ω	Static outputs	
Load: 20 mADC	$\geq 10\text{K}\Omega$	Purpose	For alarm outputs or for pulse outputs
10 VDC	By means of optocouplers, See table "Insulation between inputs and outputs"	Signal	V _{ON} 1.2 VDC/ max. 100 mA
Insulation		Insulation	V _{OFF} 30 VDC max.
Digital outputs			By means of optocouplers, See table "Insulation between inputs and outputs"
Pulse		Relay outputs	
Number of outputs	Up to 2	Purpose	For alarm outputs or for pulse outputs
Type	Programmable from 0.01 to 500 pulses per kWh/kvarh (total counters)	Type	Relay, SPST type
	Outputs connectable to the total energy meters (Wh/varh)		AC 1-5A @ 250VAC
Pulse duration	$\geq 100\text{ms}$ <120msec (ON), $\geq 120\text{ms}$ (OFF)		DC 12-5A @ 24VDC
	according to EN62053-31		AC 15-1.5A @ 250VAC
Alarm	up to 2, independent Up alarm, down alarm, in window alarm, out window alarm.		DC 13-1.5A @ 24VDC
Number of outputs	Start-up deactivation function at power-on for all kinds of alarm. All of them connectable to all variables (see the table "List of the variables that can be connected to")		See table "Insulation between inputs and outputs"
Alarm modes		RS422/RS485	
		Connections	(on request) Multidrop bidirectional (static and dynamic variables)
		Addresses	2 or 4 wires, max. distance 1200m, termination directly on the instrument
		Protocol	From 1 to 255, selectable via software MODBUS/JBUS (RTU)

Output Specifications (cont.)

Data (bidirectional) Dynamic (reading only)	System and phase variables: see table "List of variables..."	Baud-rate	4800, 9600, 19200, 38400 bits/s other characteristics like R422/RS485 port
Static (writing only) Data format	All the configuration parameters. 1 start bit, 8 data bit, no parity, 1 stop bit 4800, 9600, 19200, 38400 bits/s	Dupline Bus Address Variables	Full Dupline compatibility Programmable using CptASoft kWh, kvarh + 8 variables chosen among the available ones.
Baud-rate	By means of optocouplers, See table "Insulation between inputs and outputs"	Insulation	By means of optocouplers. See table "Insulation between inputs and outputs"
Insulation			
RS232 Type Connections Address Protocol	Halfduplex communication Point to point connection 3-wire, max. distance 15m 1 to 255 selectable via software MODBUS/JBUS (RTU)		

RS232 Configuration Bus

Connections	RJ12 (3-wire) for special cable	Insulation	By means of optocouplers, See table "Insulation between inputs and outputs"
Baud-rate	4800 bits/s		
Data format	1 start bit, 8 data bit, no parity, 1 stop bit		

CptASoft software: parameter programming and data reading

CptASoft	Multi language software to program the working parameters of the transducer and to read the energies and the instantaneous variables. Compatibility with Windows 95/98/98SE/2000/XP.	Filtering parameters Alarm variables Alarm set-points and relevant parameters Variables to be connected to the analogue outputs Scaling of analogue outputs Energies to be connected to the pulse outputs Parameters related to the pulse outputs Reset function: max/min values, energies, dmd
Working mode	Two different working modes can be selected: - management of a local RS485 network; - management of the communication from single instrument to PC (RS232); System selection: 1-2-3 phases CT/VT ratios	
Programming parameters		Data access By means of RS232 serial port, RS485 serial port or RS232 configuration port (RJ12)

Software functions

System selection System 3, unbalanced	3-phase (3-wire, 4-wire) 3-phase ARON 2-phase (3-wire) 1-phase (2-wire) 3-phase (3-wire, 4-wire) 3-phase (3-wire) "1CT+1VT" 3-phase (3-wire) "1CT+3VT" 3-phase (4-wire) "1CT+1VT" 3-phase (4-wire), phase to neutral voltage measurement 1-phase (2-wire)	Transformer ratio CT VT (PT)	1 to 60 000 1.0 to 6 000.0
System 3, balanced		Filter Operating range Filtering coefficient Filter action	0 to 100% of the retransmitted scale 1 to 32 Measurements, alarms, serial output (fundamental variables: V, A, W and their derived ones).
System 1, balanced			



Software functions (cont.)

Alarms

Working mode

"OR" or "AND" or "OR+AND" functions (see "Alarm parameter and logic" page). The user can freely program up to 16 total alarms. (out1+out2). The alarms can be connected to any variables available in the table "List of the variables that can be connected to"

Reset

The following resets are available by means of the configuration software:
- all the maximum/min values:

- W dmd max, VA dmd max, A₁ max, A₂ max, A₃ max, W_{L1} max, W_{L2} max, W_{L3} max, W sys max, A₁ dmd max, A₂ dmd max, A₃ dmd max, VA sys dmd max, W sys dmd max, PF₁ min, PF₂ min, PF₃ min
- all the counters: total kWh, partial kWh, total kvarh, partial kvarh, hour counters
- reset of all the above mentioned variables in a single command

Power Supply Specifications

AC/DC voltage

90 to 260VAC/DC
18 to 60VAC/DC

Power consumption

AC: 2.5 VA
DC: 2W

General Specifications

Front LED's

Power on
Diagnostics
RS485/RS422/RS232

Green

Dupline bus

TX data (Green)
RX data (Red)
TX data (Green)
RX data (Red)

Alarm outputs

1st output activation (Green)
2nd output activation (Red)

Pulse outputs

1st output activation (Green)
2nd output activation (Red)

Analogue outputs

Output signal within the programmed scale (Green)
Output signal exceeding 110% of full scale (Red)

Dielectric strength

4kVAC_{RMS} (for 1 min)

EMC

Emissions

EN61000-6-3, EN60688 residential environment, commerce and light industry
EN61000-6-2 industrial environment.

Pulse voltage (1.2/50μs)

EN61000-4-5

Safety standards

IEC60664, IEC61010-1
EN60664, EN61010-1

Measurement standards

IEC60688, EN60688,
EN62053-31, EN62053-23

Approvals

CE, cURus, CSA

Connections 5(6) A

Max cable cross sect. area

Screw-type

2.5 mm²

Housing

Dimensions (WxHxD)

45 x 83.5 x 98.5 mm

Material

ABS
self-extinguishing: UL 94 V-0

Mounting

DIN-rail

Protection degree

IP20

Weight

Approx. 200 g (pack. incl.)

Operating temperature

0° to +50°C (32° to 122°F)
(RH < 90% non condensing)

Storage temperature

-10° to +60°C (14° to 140°F)
(RH < 90% non condensing)

Overvoltage category

Cat. III (IEC 60664, EN60664)

Insulation (for 1 minute)

4kVAC_{RMS}
between measuring inputs and power supply.
4kVAC/DC @ I ≥ 3mA
between measuring inputs and RS485/RS232/
programming port (RJ12)
4kVAC_{RMS} between power supply and
RS485/RS232/programming port (RJ12)

List of the variables that can be connected to:

- RS485/RS422/RS232 communication port
- Analogue outputs ("max" variables, "energies" and "hour counter" excluded)
- Alarm outputs ("max" variables, energies and "hour counter" excluded)
- Pulse outputs (only "energies")
- Dupline bus (only "total energies" + up to 8 selectable variables)

No	Variable	1-phase system	2-phase system	3-ph. 4-wire balanced sys.	3-ph. 4-wire unbal. sys.	3-ph. 3-wire bal. sys.	3-ph. 3-wire unbal. sys.	Notes
1	V L1	X	X	X	X	O	O	
2	V L2	O	X	X	X	O	O	
3	V L3	O	O	X	X	O	O	
4	V L-N sys	O	X	X	X	O	O	Sys = system
5	V L1-2	O	X	X	X	X	X	
6	V L2-3	O	X	X	X	X	X	
7	V L3-1	O	O	X	X	X	X	
8	V L-L sys	O	X	X	X	X	X	Sys = system
9	A L1	X	X	X	X	X	X	#
10	A L2	O	X	X	X	X	X	#
11	A L3	O	O	X	X	X	X	#
12	Amax/ Admd max	X	X	X	X	X	X	◆ Highest value among the 3-ph
13	An	O	X	X	X	X	X	
14	W L1	X	X	X	X	O	O	◆
15	W L2	O	X	X	X	O	O	◆
16	W L3	O	O	X	X	O	O	◆
17	W sys	O	X	X	X	X	X	Sys = system
18	var L1	X	X	X	X	O	O	
19	var L2	O	X	X	X	O	O	
20	var L3	O	O	X	X	O	O	
21	var sys	O	X	X	X	X	X	Sys = system
22	VA L1	X	X	X	X	O	O	
23	VA L2	O	X	X	X	O	O	
24	VA L3	O	O	X	X	O	O	
25	VA sys	O	X	X	X	X	X	Sys = system
26	PF L1	X	X	X	X	O	O	★
27	PF L2	O	X	X	X	O	O	★
28	PF L3	O	O	X	X	O	O	★
29	PF sys	O	X	X	X	X	X	Sys = system
30	Hz	X	X	X	X	X	X	
31	Phase seq.	O	O	X	X	X	X	
32	ASY L-N	O	X	X	X	X	X	
33	ASY L-L	O	X	X	X	X	X	
34	VA sys dmd	X	X	X	X	X	X	Sys = system ◆
35	W sys dmd	X	X	X	X	X	X	Sys = system ◆
36	A L1 dmd	X	X	X	X	X	X	dmd = (*)
37	A L2 dmd	O	X	X	X	X	X	dmd = (*)
38	A L3 dmd	O	O	X	X	X	X	dmd = (*)
39	VA L1 dmd	X	X	X	X	X	X	dmd = (*)
40	VA L2 dmd	O	X	X	X	X	X	dmd = (*)
41	VA L3 dmd	O	O	X	X	X	X	dmd = (*)
42	W L1 dmd	X	X	X	X	X	X	# dmd = (*)
43	W L2 dmd	O	X	X	X	X	X	# dmd = (*)
44	W L3 dmd	O	O	X	X	X	X	# dmd = (*)
45	kWh	X	X	X	X	X	X	Total and partial
46	kvarh	X	X	X	X	X	X	Total and partial
47	hours	X	X	X	X	X	X	

(X) = available (O) = not available

(◆) These variables are available also for the MAX values stored in the EEPROM when the instrument switches off.

(★) These variables are available also for the MIN values stored in the EEPROM when the instrument switches off.

(*) dmd value integrated in a programmed time interval.

(#) The variables are available also for the max values. When the instrument switches off, the values are not stored.


Alarm parameters and logic



- Block enable.
- Controlled variable (VLN, ...).
- Alarm type (up, down, in window alarm, out window alarm).
- Activation function.




- ON set-point.
- OFF set-point.
- ON delay.
- Logical function (AND, OR).
- Digital output (1, 2).

A, B, C... up to 16
parameter control blocks.



Note: any alarm working mode can be linked to the "start up deactivation" function which disables only the first alarm after power on of the transducer.

AND/OR logical alarm examples:



Function Description

Input and output scaling capability. Working of the analogue outputs (y) versus input variables (x)

Figure A

The sign of measured quantity and output quantity remains the same. The output quantity is proportional to the measured quantity.




Figure C

The sign of measured quantity and output quantity remains the same. With the measured quantity being zero, the output quantity already has the value $Y_1 = 0.2 Y_2$. Live zero output.




Figure B

The sign of measured quantity and output quantity remains the same. On the range $X_0 \dots X_1$, the output quantity is zero. The range $X_1 \dots X_2$ is delineated on the entire output range $Y_0 = Y_1 \dots Y_2$ and thus presented in strongly expanded form.





Figure D

The sign of the measured quantity changes but that of the output quantity remains the same. The output quantity steadily increases from value X_1 to value X_2 of the measured quantity.



Insulation between inputs and outputs

	Measuring Input	Relay Output	Open collector output	Dupline output	Analogue Output	RS232/RS485	RS232 (RJ12)	90-260VAC/DC Power supply	18-60VCA/CC Power supply
Measuring input	-	4kV	2,5kV @ $I \geq 3mA$	2,5kV	2,5kV @ $I \geq 3mA$	2,5kV @ $I \geq 3mA$	2,5kV @ $I \geq 3mA$	4kV	4kV
Relay output	4kV	-	-	-	-	-	4kV	4kV	4kV
Open collector output	2,5kV @ $I \geq 3mA$	-	-	-	-	-	4kV	4kV	4kV
Dupline output	2,5kV	-	-	-	-	-	2,5kV	2,5kV	2,5kV
Analogue output	2,5kV @ $I \geq 3mA$	-	-	-	-	-	4kV	4kV	4kV
RS232/RS485	2,5kV @ $I \geq 3mA$	-	-	-	-	-	4kV	4kV	4kV
RS232 (RJ12)	2,5kV @ $I \geq 3mA$	4kV	4kV	2,5kV	4kV	4kV	-	4kV	4kV
90-260 VAC/DC	4kV	4kV	4kV	2,5kV	4kV	4kV	4kV	-	-
18-60 VAC/DC	4kV	4kV	4kV	2,5kV	4kV	4kV	4kV	-	-

NOTE: in case of fault of first insulation the current from the measuring input to the ground is lower than 2mA.


Waveform of the signals that can be measured

Figure A
Sine wave, undistorted

Fundamental content 100%
Harmonic content 0%
 $A_{rms} = 1.1107 \text{ A}$




Figure B
Sine wave, indented

Fundamental content 10...100%
Harmonic content 0...90%
Frequency spectrum: 3rd to 16th harmonic
Additional error: <1% FS





Figure C
Sine wave, distorted


Fundamental content 70...90%
Harmonic content 10...30%
Frequency spectrum: 3rd to 16th harmonic
Additional error: <0.5% FS

Accuracy

kWh, accuracy (RDG) depending on the current



kvarh, accuracy (RDG) depending on the current

**Used calculation formulas****Phase variables**

Instantaneous effective voltage

$$V_{1N} = \sqrt{\frac{1}{n} \cdot \sum_1^n (V_{1N})_i^2}$$

Instantaneous active power

$$W_1 = \frac{1}{n} \cdot \sum_1^n (V_{1N})_i \cdot (A_1)_i$$

Instantaneous power factor

$$\cos\phi_1 = \frac{W_1}{VA_1}$$

Instantaneous effective current

$$A_1 = \sqrt{\frac{1}{n} \cdot \sum_1^n (A_1)_i^2}$$

Instantaneous apparent power

$$VA_1 = V_{1N} \cdot A_1$$

Instantaneous reactive power

$$VAr_1 = \sqrt{(VA_1)^2 - (W_1)^2}$$

System variables

Equivalent three-phase voltage

$$V_\Sigma = \frac{V_{12} + V_{23} + V_{31}}{3}$$

Voltage asymmetry

$$ASY_{LL} = \frac{(V_{LL\ max} - V_{LL\ min})}{V_{LL} \sum}$$

$$ASY_{LN} = \frac{(V_{LN\ max} - V_{LN\ min})}{V_{LN} \sum}$$

Three-phase reactive power

$$VAr_\Sigma = (VAr_1 + VAr_2 + VAr_3)$$

Neutral current

$$An = \bar{A}_{L1} + \bar{A}_{L2} + \bar{A}_{L3}$$

Three-phase active power

$$W_\Sigma = W_1 + W_2 + W_3$$

Three-phase apparent power

$$VA_\Sigma = \sqrt{W_\Sigma^2 + VAr_\Sigma^2}$$

Three-phase power factor (TPF)

$$\cos\phi_\Sigma = \frac{W_\Sigma}{VA_\Sigma}$$

Energy metering

$$kWh_i = \int_{t_1}^{t_2} P_i(t) dt \equiv \Delta t \sum_{n_1}^{n_2} P_{i,n}$$

$$kVarh_i = \int_{t_1}^{t_2} Q_i(t) dt \equiv \Delta t \sum_{n_1}^{n_2} Q_{i,n}$$

Where:


i= considered phase (L1, L2 or L3)

P= active power; Q= reactive power;


t_1, t_2 = starting and ending time points of consumption recording; n= time unit; Δt = time interval between two successive power consumptions;

n_1, n_2 = starting and ending discrete time points of consumption recording

Wiring diagrams "system type selection: 3"




F= 630 mA T (18 to 60VAC/DC)
 125 mA T (90 to 260VAC/DC)




Wiring diagrams "system type selection: 3" (cont.)


3-ph, 4-wire, unbalanced load Fig. 7



3-ph, 4-wire, unbalanced load Fig. 8




3-ph, 3-wire, unbalanced load Fig. 9




$F = 630 \text{ mA T (18 to 60VAC/DC)}$
 $125 \text{ mA T (90 to 260VAC/DC)}$


3-ph, 3-wire, unbalanced load Fig. 10






3-ph, 3-wire, balanced load Fig. 11



3-ph, 4-wire, balanced load Fig. 12




Wiring diagrams "system type selection: 1"



F= 630 mA T (18 to 60VAC/DC)
125 mA T (90 to 260VAC/DC)

Outputs



Analogue output 0-20mA




Fig. 17

Analogue output 0-10V




Fig. 18

Relay out.




Fig. 19

NOTE: the analogue outputs are not insulated among each other.




Fig. 20






Fig. 21

Open collector outputs: The load resistance (Rc) must be calculated so that the closed contact current is lower than 100mA; the VDC voltage must be lower than or equal to 30V. VDC: power supply voltage (external). Vo+: positive output contact (open collector transistor). GND: ground output contact (open collector transistor).


RS485 serial port and one relay connections



2-wire connection of RS485 serial port. The terminalization must be carried out only on the last instrument of the network




4-wire connection of RS485 serial port, the terminalization must be carried out only on the last instrument of the network



2-wire connection of RS485 serial port, the terminalization must be carried out only on the last instrument of the network


RS232 Serial port connection

Easy programming




RJ12 communication port for parameters programming. The configuration of the transducer can be easily performed by means of CptASoft. CptASoft-kit includes also 1m long connection cable (RJ12 6-pole / RS232 9-pole female).

Outputs connections



Front Panel Description



1. Front panel
2. Power ON LED
3. Diagnostics LED
4. Configuration bus (RJ12 connector)
5. Connections screw terminals

Dimensions

