

Professionally approved products.

Datasheet

160 mm Tri-Angle Type Needle File

RS Stock number 541-6949



Specification

Material:

Press moulded high carbon steel for needle file blade

Finish:

Neutral colour needle file blades, press cut notch of blade.

Contents:

5pc-160mm tri-angle type needle file with taper end & knurled hand grip of file, sealed vinyl pouch

Feature:

High quality precision needle files for the fine abrasion, profile cutting and finishing of many common workshop materials

Each file has a different cross-section as shown and except for the 'hand' and 'warding' which are squared off, all taper to a fine point

Overall length 160mm, cutting face 28 teeth per cm (cut no. 1)

Round file has a diameter of 6.35mm (0.25in)