# Dupline Plug & Play Master Module Interface for Allen Bradley PLC Type G 3496 0006





- Allen Bradley Master
- Plug and play: Automatic communication with specific PLC/Controllers
- Built-in normal Dupline® Channel Generator
- 128 I/O's and DC power supply on 3 wires
- RS232 port for interfacing to control system
- Split-I/O mode selectable (128 inputs and 128 outputs)
- LED-indications for supply, Dupline carrier and Comport TX
- Galvanically isolated Com-port supplied by internal DC/ DC converter

### **Product Description**

G 3495 0006 is designed as a cost-effective solution for interfacing Dupline® I/O's to Allen Bradley PLCs – the SLC 500 and Micrologix families. It performs three functions:

Dupline® channel generator, power supply synchronization (enables 3-wire system with supply) and RS232 interface.

Ordering Key	G 3496 0006 700
Type: Dupline®  H4-Housing  Combined module  Interface type  DC supply	

### **Type Selection**

Supply	PLC Interface Conformance	Ordering no.
20-30 VDC	MicroLogix 1000, 1200 and 1500. SLC5-03, SLC5-04 and SLC5-05.	G 3496 0006

### **Input/Output Specifications**

Power Output Output voltage Output current Short circuit protection Output voltage drop	20-30 VDC (pulsating) < 3.0 A @ 50°C 4 A quick acting fuse < 1.0 V
Dupline® carrier Output voltage Current Short circuit protection Scan time 128 channels 64 channels	8.2 V (pulsating) < 60 mA Yes 132.2 ms 69.8 ms
Communication Port Standard Connection Dielectric voltage Com-port-Dupline® Protocol Channel Configuration in PLC Driver Source ID Baud rate Data bits Start bit Stop bit Parity Flow-control Error detection Pin assignment RS232 TX Rx GND	RS232 9 pole female Sub-D  1 kVAC (rms) DF1  DF1 Full Duplex 1 9600 8 - 1 None None CRC or BCC

### **Supply Specifications**

Power supply	Overvoltage cat. III (IEC 60664)
Operational voltage (V <sub>in</sub> )	20-30 VDC
Reverse polarity protection	None
Current consumption	< 150 mA + Power load
Power consumption	< 5 W
Transient protection voltage	800 V
Dielectric voltage	
Supply - Dupline®	None
Supply - Com-port	1 kVAC (rms)

**Note:** Use individual power supplies for all G349600xx700, as the input are not galvanic isolated from each other.

## **General Specifications**

Power ON delay	2 s
Indication for Com-port TX Supply ON Dupline® carrier	LED, red LED, green LED, yellow
Environment Pollution degree Operating temperature Storage temperature	2 (IEC 60664) 0° to +50°C (+32° to +122°F) -50° to +85°C (-58° to +185°F)
Humidity (non-condensing)	20 to 80%
Mechanical resistance Shock Vibration	15 G (11 ms) 2 G (6 to 55 Hz)
Dimensions	H4-Housing
Weight	100 g



### **Mode of Operation**

The Dupline® Master Module (DMM) controls a 3-wire bus with signal, DC-power and common GND. The DMM is connected to a standard DC-supply, which it synchronizes with the Dupline® carrier signal before it is output to supply. The synchronization is necessary in order to enable the Dupline® and DC-supply to share the GND-wire.

The Dupline® Master Module is a Dupline® Channel Generator with the function of a master. This means that the 128

Dupline® I/0's will be read/written by the DMM and then sent to the PLC.

The DMM can run in two different modes – Normal mode and split I/O mode. In Normal mode, Dupline® operates as a peer-to-peer system, where the channel generator automatically establishes a connection between Dupline® inputs and Dupline® outputs which are coded to the same Dupline® address. If e.g. an input coded for B5 is activated, the output(s) coded for B5

will also be activated.

Consequently, a Dupline®-output can either be activated through the output-data received on DMM or by an active Dupline® input coded for the same Dupline®-address. In "Split I/O" mode, the channel generator treats the Dupline® inputs and Dupline® outputs independently. If e.g. an input coded for B5 is activated, the DMM will make the information available for the PLC (like in normal mode), but it will not automatically activate the

Dupline® output(s) coded to B5. The Dupline® outputs are controlled exclusively through the output data received from the PLC. In this mode, up to 128 Dupline® inputs and 128 Dupline® outputs are available, since an input and an output coded to the same Dupline® address can operate independently.

### **Memory Mapping**

#### Configuration of data file in RSLogix 500 Programming

DATA FILE	MicroLogix & SLC		
	Type: 1000	Type: Other	
File	7	9	
Туре	N (Integer)	N (Integer)	
Elements	16*	16*	

<sup>\*</sup>Registers 0-7: Dupline® Input Channels A1 to P8. Registers 8-15: Dupline® Output Channels A1 to P8.

# Table of the memory mapping to the PLC (Except MicroLogix 1000)

Dupline® Channel	MicroLogix & SLC		Dupline® Channel	MicroLog	jix & SLC
	Read	Write		Read	Write
A1	N9: 0/0	N9: 8/0	E1	N9: 2/0	N9: 10/0
A2	N9: 0/1	N9: 8/1	F1	N9: 2/8	N9: 10/8
A3	N9: 0/2	N9: 8/2	G1	N9: 3/0	N9: 11/0
A4	N9: 0/3	N9: 8/3	H1	N9: 3/8	N9: 11/8
A5	N9: 0/4	N9: 8/4	I1	N9: 4/0	N9: 12/0
A6	N9: 0/5	N9: 8/5	J1	N9: 4/8	N9: 12/8
A7	N9: 0/6	N9: 8/6	K1	N9: 5/0	N9: 13/0
A8	N9: 0/7	N9: 8/7	L1	N9: 5/8	N9: 13/8
B1	N9: 0/8	N9: 8/8	M1	N9: 6/0	N9: 14/0
B8	N9: 0/15	N9: 8/15	N1	N9: 6/8	N9: 14/8
C1	N9: 1/0	N9: 9/0	01	N9: 7/0	N9: 15/0
D1	N9: 1/8	N9: 9/8	P1	N9: 7/8	N9: 15/8

### **Dip-Switch Setting**

Sw.5

Sw.2	On:	Checksum CRC
	Off:	Checksum BCC
•	_	0 111 1/0 01 1 0

Sw.4 On: Split I/O Channel Generator Mode Off: Normal Dupline® Monostable Channel

Generator Mode

On: 64 Dupline® channels
Off: 128 Dupline® channels

Sw.6 On: Maintain data to Dupline® receivers in

case of communication failure

Off: Clear data to Dupline® receivers in case of communication failure after 75 Dupline® scans

# Table of the memory mapping to the PLC (Only MicroLogix 1000)


Dupline® Channel	MicroLogix 1000		Dupline® Channel	MicroLo	gix 1000
	Read	Write		Read	Write
A1	N7: 0/0	N7: 8/0	E1	N7: 2/0	N7: 10/0
A2	N7: 0/1	N7: 8/1	F1	N7: 2/8	N7: 10/8
A3	N7: 0/2	N7: 8/2	G1	N7: 3/0	N7: 11/0
A4	N7: 0/3	N7: 8/3	H1	N7: 3/8	N7: 11/8
A5	N7: 0/4	N7: 8/4	I1	N7: 4/0	N7: 12/0
A6	N7: 0/5	N7: 8/5	J1	N7: 4/8	N7: 12/8
A7	N7: 0/6	N7: 8/6	K1	N7: 5/0	N7: 13/0
A8	N7: 0/7	N7: 8/7	L1	N7: 5/8	N7: 13/8
B1	N7: 0/8	N7: 8/8	M1	N7: 6/0	N7: 14/0
B8	N7: 0/15	N7: 8/15	N1	N7: 6/8	N7: 14/8
C1	N7: 1/0	N7: 9/0	01	N7: 7/0	N7: 15/0
D1	N7: 1/8	N7: 9/8	P1	N7: 7/8	N7: 15/8



### **Pin Assignment**

DMM G34960006	Allen Bradley PLC type MicroLogix
9P D-SUB Male	8-pin mini-DIN Male
1 (Tx)	4 (Rxd)
9 (Rx)	7 (Txd)
5 (GND)	2 (GND)

DMM G34960006	Allen Bradley PLC type SLC	
9P D-SUB Male	9-pin D-SUB Male	
1 (Tx)	2 (Rxd)	
9 (Rx)	3 (Txd)	
5 (GND)	5 (GND)	



#### **Accessories**

Type MicroLogix Cable Sub-D 9M/8 mini Din Type SLC Cable Sub-D 9M/9M

RS-232-AB1

RS-232-AB2

# Hardware fault

No Dupline® Carrier-LED

**Installation Hints** 

**Slow-flashing TX-LED** 

Dupline® short circuit

Short circuit between the two Dupline® wires.

Check the wiring.

### **Additional Information**

Scope of supply

1 x Master Module

G3496 0006 700

## **Dimensions (mm)**

