

Professionally approved products.


## Datasheet

# Single Mode Simplex Fibre Optic Patch Panel

RS Stock number 738-8552



## Dimensions (mm)



## Specification

1. INSERTION LOSS: 0.75 dB MAX.
2. OPERATION TEMP: -20 C TO +70 C.
3. PRODUCT COMES WITH DUST CAPS. (NOT SHOWN)
4. MATERIALS:
  - SLEEVE:
    - SINGLE-MODE - CERAMIC (ZIRCONIA)
    - MULTI-MODE - PHOSPHORUS BRONZE
  - HOUSING - DELRIN, BLACK
  - ADAPTER - THERMOPLASTIC
  - SCREWS - STEEL, NICKEL PLATED
  - ADAPTER MOUNTING CLIPS - STAINLESS STEEL
5. FOR MOUNTING SCREWS TO BE SHIPPED WITH ASSEMBLY AND INDIVIDUALING PACKAGING, ADD SUFFIX -PKG TO PART NUMBER.
6. WHEN MOUNTING ASSEMBLY, USE A SCREW TORQUE OF 10 INCH-POUNDS MAXIMUM.
7. THIS PRODUCT IS RoHS COMPLIANT.