


Data sheet

N Plug to F Jack Adapter

RS stock No: 7581613



1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-11 GHz
 1.2 NOMINAL IMPEDANCE: 50 OHMS
 1.3 WORKING VOLTAGE: 1000 VOLTS MAX.
 1.4 PROOF VOLTAGE: 2500 VOLTS
 1.5 VSWR: 1.1 MAX. @6 GHz
 1.3 MAX. @11 GHz

2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
 2.2 CENTER CONTACT: BERYLLIUM COPPER PER ASTM B196 UNS C17300
 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

4.0 MECHANICAL

- 4.1 INTERFACE IN ACCORDANCE WITH: MIL-STD-348A

5.0 ENVIRONMENTAL

- 5.1 OPERATING TEMPERATURE RANGE: -85° C TO +185° C

5	O-RING	SILICONE	1	BLACK
4	INSULATION	TEFLON	1	NONE
3	CENTER CONTACT	BERYLLIUM COPPER	1	GOLD 3 μ" MIN.
2	BODY	BRASS	1	WHITE BRONZE 80 μ" MIN.
1	CHASSIS	BRASS	1	WHITE BRONZE 80 μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by _____ DATE: _____

DESCRIPTION		STRAIGHT BULKHEAD N JACK RECEPTACLE									
製圖	DRAWN	TOLERANCE		品名	61-18	T.G.WB	日期	DATE	版次	REV.	
	Cina	X	±0.2	TITLE	ROHS COMPLIANT (50Ω)		02.16.12'		A-0		
檢圖	CHECK	XX	±0.1	單位	DWG.NO.		61-0004				
	Arc	XXX	±0.05	mm(in)							
認定	APPROVAL	ANGLE ±5°		SCALE							
	Angela	比例		3:1							



