



## Description

- 2.4mm PVC insulation
- Conductor is high strength 7-strand tinsel wire for strength and durability
- Low-profile head helps prevent cord from being knocked off
- Built-in 10mm stud fits socket on mat
- 1 megohm ( $1 \times 10^6$  ohms) resistor in conical head

ITEM	DESCRIPTION
798-9335	10mm Socket, 4.5m long, 1 megohm ( $1 \times 10^6$ ohms)

"EPA ground cords shall be used to make electrical connections between groundable points and the EPA ground facility.

Where a single resistor is used in the EPA ground cord, this shall be located near the groundable point. Where more than one resistor is used, a resistor of a minimum resistance value of one half the total resistance shall be located near the groundable point.

When accessible, the EPA ground cord and its groundable point connection shall be shrouded by insulating material." (EN 61340-5-1 section 5.3.4 EPA ground cords)

*Unless otherwise noted, tolerance  $\pm 10\%$*

Specifications and procedures subject to change without notice.



Made in the  
United Kingdom



## Straight Cords with Conical Head, 10mm Socket, Ring Terminal

**RS COMPONENTS LTD.**  
BIRCHINGTON ROAD, CORBY,  
NORTHANTS, NN17 9RS, UK

**Drawing Number**  
**RS-798-9335**

**DATE:**  
February  
2014