


Approvals: 

C14 Inlet with double fuse

Specifications

| | |
|--|--------------------------------|
| Current & voltage rating: | 10A, 250 VAC |
| Product Description: | Inlet with double fuse |
| Panel thickness: | NA |
| Permissible temperature - For soldering: | 270 deg.C for 5 seconds max. |
| Permissible temperature - With/without load: | 0 to 70deg. C |
| Approvals: | CE |
| Reference Standard: | IEC 60320-1 |
| Material - Body: | Nylon |
| Material - Terminals: | Copper Alloy, Tin plating |
| Terminals: | Solder-type / Fast on 4.8X 0.8 |
| Mounting: | Panel, Screw type |
| HV Breakdown test for 1 Minute: | 2 KVAC |
| Insulation Resistance at 500 VDC: | 1000 Mohms min. |
| Contact Resistance (Initial): | 10 mohms max. |