



Professionally approved products.

Product datasheet

Cleanroom A4 Technical Paper



FEATURES AND BENEFITS

- ISO 5 Cleanroom processed
- Low Chloride and other ionic contamination
- Formulated without Magnesium Silicate
- Excellent IPA resistance material
- Compatible to most inks in writing without smearing
- Ultra low ionic contamination
- Ultra low particle and fiber generation
- Excellent heat resistance material for laser printing and photocopiers
- ROHS compliant
- Available sterile by Gamma Irradiation

APPLICATIONS

- Note taking
- Printing
- Form & Logsheet

PHYSICAL CHARACTERISTICS

PROPERTY	TYPICAL VALUE	TEST METHOD
Basis Weight	76.7 gsm + 4%	---
Caliper	96 + 8 um	---
Surface Resistivity	5.5×10^{10} Ohms/sq	EOS/ESD-S11.11-1993
Tear Strength (MD)	> 300 mN	Elmendorf Tear Test
Tear Strength (CD)	> 400 mN	Elmendorf Tear Test
Opacity	> 85%	---





CONTAMINATION CHARACTERISTICS

ANION	TYPICAL VALUE	CATION	TYPICAL VALUE
Cl	0.004 ug/cm ²	Li	Not Detected
F	0.012 ug/cm ²	Na	0.10 ug/cm ²
Br	0.002 ug/cm ²	NH ₄	0.03 ug/cm ²
NO ²	Not Detected	K	0.14 ug/cm ²
NO ³	0.001 ug/cm ²	Mg	0.08 ug/cm ²
PO ⁴	Not Detected	Ca	2.00 ug/cm ²
SO ⁴	0.041 ug/cm ²		

RELEASABLE PARTICLES	TYPICAL VALUE
Flexing test (> 0.5 um)	20 counts/ft ³ /sheet
At Rest (>0.5um)	20 counts/ft ³ /sheet
Talc Check (by SEM-EDX)	< 5 particles

ITEM 8295212 White

ITEM 8295215 Blue

ITEM 8295219 Pink

ITEM 8295225 Yellow

ITEM 8295234 Green