



Professionally approved products.

Product datasheet

Cleanroom Lined Notebook



Spiral-bound cleanroom notebook featuring antistatic covers to prevent static charge build-up

- Cleanroom processed and cleanroom packaged with cleanroom bags
- Cleaned and packed in controlled ISO 5 Cleanroom Environment

COVERS

- High-density polypropylene material which offer impregnated antistatic properties
- Precision cut with round edge corners
- Excellent chemical resistance material

PAPER

- Durable Clean Image cleanroom paper
- Low-sodium inks printed
- 50 sheets per book

BENEFITS

HIGH DENSITY POLYPROPYLENE COVERS

- Excellent chemical resistance material
- Antistatic material to prevent static charge build-up
- Round corners construction to prevent tearing of gloves by sharp edges

APPLICATIONS

- Note-taking in critical environment
- Logbook





TECHNICAL DATA

CLEANROOM PAPER CONTAMINATION CHARACTERISTICS			
Ion Chromatography (IC)			
ANION	TYPICAL VALUE	CATION	TYPICAL VALUE
Cl	0.3191 ug/cm ²	Li	NOT DETECTED
F	0.0016 ug/cm ²	Na	2.23 ug/cm ²
Br	NOT DETECTED	NH ₄	NOT DETECTED
NO ²	0.0017 ug/cm ²	K	0.11 ug/cm ²
NO ³	0.0128 ug/cm ²	Mg	0.04 ug/cm ²
PO ⁴	NOT DETECTED	Ca	1.10 ug/cm ²
SO ⁴	0.1517 ug/cm ²		
Liquid Particle Count (LPC) Wet Test (> 0.5 um)		190 counts/cm ²	
Airborne Particle Count (APC) Dry Test (0.5um)		50 counts/ft ³ /cm ²	

COVER

Extractable Organic

Silicon

NOT DETECTED

Amide

NOT DETECTED

ESD PROPERTIES

Surface Resistivity

4.9 x 10¹⁰ ohms/sq

Static Charge Generation

<10v

ITEM 8295228 A4

ITEM 8295221 A5