

Professionally approved products.

## Product Datasheet PTFE Insulated Equipment Wire (Type C) 19/0.45mm SPC

EN

8417471





Characteristics: Relevant Standards: BS 3G 210:1996 Rated Voltage: 1000 Vrms Working Temperature (°C): -75 to 200 °C

**Construction:** Inner Conductor: Silver plated copper Insulation: PTFE

## **Specification**:

	Cor	Insulation Thickness (mm)		Overall Diameter (mm)		Conductor resistance (Ω/Km, at 20°C)	Mass	Long term current Rating (A)		
Size AWG	Area (mm2)	0/D (mm)	Stranding (mm)	Min.	Max.	Min.	Max.	SPCW Max.	Max (Kg/Km)	Max.
12	3.022	2.25 0	19/0.45	0.33	0.40	2.91	3.31	6.28	38.50	35.0
*Current ratings are based on a temperature rise of 40°C (single wire in free air)										

## **Product Range:**

RS Code Description 8417471 PTFE C 19/0.45 pink 25m