




Part No.	"A" mm	"B" mm	"C" mm	"D" mm	"E" mm	"F" mm	"G" mm
MWSB-1-01A-RT	7.2	3.0	6.9	4.3	-	2.0	9.5
MWSEB-1-01A-RT	4.1	1.0	7.1	4.6	1.5	2.0	9.4
MWSEB-2-01A-RT	6.1	2.8					
MWSEB-3-01A-RT	7.4	3.0	9.1	6.4	2.0	4.1	12.7
MWSEB-4-01A-RT	9.1	4.1	10.7	7.9			
MWSEB-5-01A-RT	11.2	6.1	11.9	8.9			
MWSEB-6-01A-RT	13.0	7.6					

UL N° E71558

MWSB



MWSEB



MWSB/MWSEB

MINIATURE WIRE SADDLE ON BASE

Material: Nylon 6/6 - natural, UL 94 V-2, RMS-01 or Nylon 6/6 - natural, UL 94 V-0, RMS-19
 Adh. Tape: Working temperature -20°C – +50°C
 Std. Pk.: 1.000 pcs.

Note:

MWSEB	1	01	A-RT
Part	Size	Material Code	with Tape