

Professionally approved products.

Datasheet

RS Electric Torque Screwdriver



DC electric torque driver supplied with a soft start power supply.

- Swiss made brushless motor for cooler running and zero Carbon partials
- Ideal for clean environments
- ESD safe body for electronic assembly work

Supplied with: GB plug with Euro adaptor, cables, PH0 & PH1 Phillips bit.

Technical Specifications

Driver	849-2016	849-2025	849-2028
Bit Drive	1/4in Hex	1/4in Hex	1/4in Hex
Power	60W	60W	60W
Torque Range	0.05 - 0.5Nm	0.15 - 1.2Nm	0.4 - 2.0Nm
No Load Speed	700 - 1000 rpm	700 - 1000 rpm	700 - 1000 rpm
Suitable Machine Screws	1.0 - 2.6mm/ 0.04 - 0.10in	1.4 - 3.0mm/ 0.06 - 0.12in	2.6 - 4.0mm/ 0.10 - 0.16in
Suitable Tapping Screws	1.0 - 2.3mm/ 0.04 - 0.09in	1.4 - 2.6mm/ 0.06 - 0.10in	2.3 - 3.5mm/ 0.09 - 0.14in
Length	227mm/ 8.9in	227mm/ 8.9in	227mm/ 8.9in
Weight	412g/ 0.9lb	412g/ 0.9lb	412g/ 0.9lb



Professionally approved products.

Power Supply	
Power	60W
Frequency	50/60Hz
Input Voltage VAC	100 - 240V
Output Voltage VDC	20 - 30V
Output Pin	5 pin
Internal Signal Input	Switching Signal/ Shut Off Signal
External Signal Input	Switching Signal
Dimensions	164 x 64 x 42mm
Weight	300g