



## BEFESTIGUNGSTECHNIK FÜR LEITERPLATTEN

Gewinde "M1" + "M2"		Längen "L" mm	"H" mm
M3	M3	5.0 / 6.0 / 7.0 / 8.0 / 9.0 / 10.0 / 11.0 bis 61,0	6.0
M4	M4	5.0 / 6.0 / 7.0 / 8.0 / 9.0 / 10.0 / 11.0 bis 60,0	8.0
Gewindetiefe „P1“ mm		3.0 / 4.0 / 4.0 / 6.0 / 8.0 / 9.0 / 10.0	



KUNSTSTOFF-ABSTANDSBOLZEN  
INNEN-/AUSSERGEWINDE



Material: Nylon 6/6 - schwarz; UL 94 HB