

Professionally approved products.

Datasheet

50/125 Optical Fibre Patchcords

RS Stock number 535-7294



Description:

Optical Fibre patchcords are a defining factor in ensuring your network performs to the highest level. A patch cord can be split into three key components;

- the connector
- the cable
- the manufacturing process.

These three areas all contribute to the performance of a patch cord, but it is the manufacturing process that defines the performance of the assembly.

Features:

- Multimode & Singlemode applications ST/SC/FC/LC/E2000/Mu connector types
- Ultra polish & angle polish options available, all terminations are manufactured to exceed performance parameters set by industry standards
- Tyco AMP approved UK manufacturing facility
- Fast turn around of non-standard requirements
- Full traceability & test certification supplied with each assembly
- 900µm tight buffered fibre optic cable

Professionally approved products. Datasheet

Patchcord Specification

Mechanical

Length: 1m to 10m \pm 10mm
Other lengths available to order

Split Length (Duplex): 150mm \pm 5mm

Product Packaging

Each patch cord is packaged individually and individually identified for traceability, test certification is supplied for each assembly.

Optical fibre and cable performance

Attenuation (dB/km)

(850/1300) 2.8/0.8

Bandwidth (MHz.Km)

(850/1300) 500/500

Sheath colour

Orange

Strength Members

Aramid strength members

Fire Performance

LSZH for Internal/External Applications

Flame Resistance IEC 60332-1

Connector Specification

Optical Performance (Multimode)

Insertion loss: Max. 0.3 dB Typical 0.2 dB

Optical Performance (MT-RJ)

Insertion loss: Max. 0.5 dB

Operating Temperature

-40°C to +85°C

Intermateability Optically and mechanically compatible with all equivalent connectors.

Compliant with IEC 874-14.

For full information on the Optronics connectors used on the FibreFab patch cords, please contact the address below for a connector data sheet.