



Standard	UL	IEC
Rated voltage	300V	250V
Rated current	8A	10A
Contact resistance	20mΩ	
Insulation resistance	500MΩ/DC500V	
With standing voltage	AC 2000V/1 Min	
<b>Mechanical</b>		
Temp. Range	-40°C~+105°C	
Temp. Range	+250°C	5秒
<b>Dimensions</b>		
Pitch	3.81mm	
Poles	2~22p	
<b>Material</b>		
Housing	PA66, UL94V-0	
Pin header	Brass, Tin plated	

linear dimension variable range tolerance	over 6 to 6	over 10 to 10	over 18 to 18	over 30 to 30	over 50 to 50	over 80 to 80	over 120 to 120	over 160 to 160	over 200 to 200	over 250 to 250	all	over 5 to 5	over 30 to 30	over 120 to 120	
	±0.1	±0.14	±0.19	±0.25	±0.32	±0.43	±0.57	±0.72	±0.88	±1.05	±1.25	0.5	0.025	0.06	0.12
	linear dimension(Tolerances Standard GB/T 14486-2008)										≡	—	□	//	L

UNITS	mm	SIZE	A4	SCALE	3:1	TITLE	21.155MHF/2-E
 THIRD ANGLE PROJECTION							